

## IE-C5ES8VG0650A40A40-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 65 m
Order No.	<a href="#">8934630650</a>
Type	IE-C5ES8VG0650A40A40-E
GTIN (EAN)	4050118300635
Qty.	1 pc(s).

Creation date March 15, 2023 8:26:33 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## IE-C5ES8VG0650A40A40-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	65 m	Length (inches)	2,559.055 inch
Net weight	2,423 g		

## Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	0 °C...50 °C		

## Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm <sup>2</sup>
Diameter of wire pair	2 mm	Insulation	PE
Insulation cross-section	1 mm	Material sheath	PVC
Number of wires	8	Overlap of shielding braid	65 %
Sheath diameter, max.	6.1 mm	Sheath diameter, min.	5.7 mm
Sheathing colour	green (RAL 6018)	Shielding	SF/UTP
Shielding braid thickness	0.1 mm	Strands	7
Wire core insulation thickness	0.25 mm	Wire material	Stranded tin-plated copper wire

## Electrical properties of cable

Capacity at 1 kHz	47 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Deviation	25 ns/100m
Loop resistance	290 Ω/km	Resistance differential	3 %
Signal propagation time	4.85 ns/m	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	10 mΩ/m at 10 MHz		

## Mechanical and material properties of cable

Abrasion resistance	good	Fire propagation	No
Halogen	Yes	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Resistance to spread of flame	in accordance with IEC 60332-1

## Plug

Plug left	RJ45, IP20, male contact, straight, Plastic, shielded	Plug right	RJ45, IP20, male contact, straight, Plastic, shielded
-----------	---	------------	---

## Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

**IE-C5ES8VG0650A40A40-E****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data****Approvals**

ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>