


## H16,0/38 ZH GN

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Twin wire-end ferrule, 29 mm, 25 mm, green |
| Order No.  | <a href="#">9037370000</a>                                   |
| Type       | H16,0/38 ZH GN   |
| GTIN (EAN) | 4008 190492847   |
| Qty.       | 50 pc(s).  |
| Packaging  | loose  |

Creation date March 1, 2023 3:31:58 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**H16,0/38 ZH GN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 1.82 g

**Technical data**

| Description of article | Twin wire end ferrule, green | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|
|------------------------|------------------------------|---------|-----------------------|

**Wire-end ferrules**

|   |            |                             |                    |
|---|------------|-----------------------------|--------------------|
| Collar height (A)                       | 17.2 mm    | Collar width (B)            | 9.5 mm             |
| Colour code                             | Weidmüller | Conductor cross-section     | 16 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 8.3 mm     | Contact surface length (L2) | 25 mm              |
| L1 in mm                                | 38 mm      | Metal sleeve thickness (S1) | 0.3 mm             |
| Plastic collar thickness (S2)           | 0.6 mm     | Stripping length            | 29 mm              |
| Wire connection cross section AWG, max. | AWG 6      |                             |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ECLASS 9.0  | 27-40-02-01 |
| ECLASS 9.1  | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E499744    |

**Downloads**

|                    |  |
|--------------------|--|
| Engineering Data   | <a href="#">CAD data – STEP</a>  |
| Engineering Data   | <a href="#">WSCAD, Zuken E3.S</a>  |
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |
| Brochures          |  |

**Data sheet**

**H16,0/38 ZH GN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

