

**STRIPPER 6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

Version	Stripping and cutting tool
Order No.	<a href="#">9046240000</a>
Type	STRIPPER 6
GTIN (EAN)	4032248298648
Qty.	1 Stück

## STRIPPER 6

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	19 mm	Depth (inches)	0.748 inch
Height	87 mm	Height (inches)	3.425 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	180 g		

### Technical data

Description of article	Stripping tool for wires up to 6 mm <sup>2</sup> / with integrated cable cutter
------------------------	---

### Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	0.08 mm <sup>2</sup>	Stripping length, max.	20 mm
Stripping range AWG, max.	10 AWG	Stripping range AWG, min.	28 AWG

### Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

### Approvals

Approvals



### Downloads

Catalogues [Catalogues in PDF-format](#)