

**LIF 6F638 RF**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



**Fully-insulated tab-connector sleeves made from PVC with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

**General ordering data**

Version	cable lug, terminal end, Insulated cable connector, 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow
Order No.	<a href="#">9200660000</a>
Type	LIF 6F638 RF
GTIN (EAN)	4032248410507
Qty.	100 pc(s).

**LIF 6F638 RF**
**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)
[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Dimensions and weights**

Depth	8.2 mm	Depth (inches)	0.323 inch
Width	24.5 mm	Width (inches)	0.965 inch
Net weight	1.9 g		

**Technical data**

Description of article	Fully-insulated tab-connector sleeves 4.0-6.0 mm <sup>2</sup>
------------------------	---

**Connectors**

Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
Dimension	6.3 x 0.8 mm	Dimension (flat blade connector)	6.3 x 0.8 mm
Identification colour	yellow	Insulation	Fully insulated
Material/plastic	PVC	Plastic collar diameter (D)	6.8 mm
Plastic collar length (b)	13 mm	Plug-in density (d3)	0.8 mm
Plug-in width (d2)	6.3 mm		

**Classifications**

ETIM 6.0	EC0005 16	ETIM 7.0	EC0005 16
ETIM 8.0	EC0005 16	ECLASS 9.0	27-44-03-92
ECLASS 9.1	27-40-02-90	ECLASS 10.0	27-44-03-92
ECLASS 11.0	27-44-03-92	ECLASS 12.0	27-44-03-92

**Approvals**

Approvals



ROHS Conform

**Downloads**

 Catalogues [Catalogues in PDF-format](#)  
 Brochures

**Data sheet**

**LIF 6F638 RF**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

