

TEMPHASER

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Version	Testing tools, Multimeter
Order No.	9427300000
Type	TEMPHASER
GTIN (EAN)	4032248407057
Qty.	1 Stück

TEMPHASER

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	39 mm	Height (inches)	1.535 inch
Width	147 mm	Width (inches)	5.787 inch
Net weight	512.1 g		

Technical data

Description of article	Measurement device set V, A, O, F, Hz, °C, °F	Version	Infrared thermometer
------------------------	---	---------	----------------------

Measuring and testing devices

AC voltage measuring range	0.2 - 600 V	Battery type	9V block battery
DC voltage measuring range	0.2 - 600 V	Display	digital
Frequency measurement	Yes	Frequency range, max.	40 kHz
Frequency range, min.	10 Hz	Measured capacitance value, max.	20 mF
Measured capacitance value, min.	20 µF	Measured temperature value, max.	750 °C
Measured temperature value, min.	-20 °C	Measuring range category	CAT III
Resistance measuring range, max.	2,000 MΩ	Resistance measuring range, min.	0.2 Ω
Selection of measuring range	Manual	Test probe	Yes
Tested and approved according to	EN/IEC 61010-1	Working temperature, max.	50 °C
Working temperature, min.	0 °C		

Classifications

ETIM 6.0	EC000069	ETIM 7.0	EC000069
ETIM 8.0	EC000069	ECLASS 9.0	27-20-03-01
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-01
ECLASS 11.0	27-20-03-01	ECLASS 12.0	27-20-03-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

TEMPHASER

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Example of use

