

TBF 49/30/21 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

Features:

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Version	TBF (polyester empty enclosure), Empty enclosure, Height: 488 mm, Width: 302 mm, Depth: 210 mm, Material: Glass fibre-reinforced polyester, Miscellaneous, Light Grey, Transparent
Order No.	9502840000
Type	TBF 49/30/21 TRSP
GTIN (EAN)	4032248027446
Qty.	1 Stück

TBF 49/30/21 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	210 mm	Depth (inches)	8.268 inch
Height	488 mm	Height (inches)	19.213 inch
Width	302 mm	Width (inches)	11.89 inch
Net weight	3,185 g		

Temperatures

Operating temperature	-50 °C...130 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	130 °C		

Cable glands, right

M12	42	M16	42
M20	36	M25	18
M32	7	M40	5
M50	5	M63	4

Cable glands, top/bottom

M12	44	M16	24
M20	20	M25	10
M32	4	M40	3
M50	3	M63	2

Certificate numbers enclosure

Certificate No. (EAC)	RUC-DE.BE02.B.00173	Certificate no. Terminal Box (EAC)	RU C-DE.BE02.B.00173 Ind. Terminal Box
-----------------------	---------------------	------------------------------------	---

General information

Access opening: height	462 mm	Access opening: width	276 mm
Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction	Enclosure attachment	6.5 mm hole in enclosure base
Flange plate	No	Impact resistance	IK08 in accordance with IEC 62208, IK10 in accordance with IEC 62262
Integral fixing	4 or 6 stud bolts M6 inner (female) thread	Lid	Yes
Lid attachment	Crosshead nylon screws	Material	Glass fibre-reinforced polyester
Number of lid screws	4	Operating temperature, max.	130 °C
Operating temperature, min.	-50 °C	Protection degree	IP66
Seal material	Polyurethane	Standards	IEC 60529, EN 60529, EN 62208, EN/IEC 61439-2
Surface finish	Miscellaneous	Torque for lid screws	1.5 Nm
Toxicity	Free from halogens	UL 94 flammability rating	V-2

horizontal assembly

WDU 10 / ZDU 10	3x22	WDU 16 / ZDU 16	3x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x44	WDU 35 / ZDU 35	3x14
WDU 4 / ZDU 4	3x37	WDU 6 / ZDU 6	3x28

Erstellungs-Datum May 25, 2023 11:26:10 AM CEST

TBF 49/30/21 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

vertical assembly

WDU 10 / ZDU 10	2x41	WDU 16 / ZDU 16	2x29
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x80	WDU 35 / ZDU 35	2x25
WDU 4 / ZDU 4	2x67	WDU 6 / ZDU 6	2x51

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	RU C-DE.BE02.B.00173 - Ind. Terminal Box
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

TBF 49/30/21 TRSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

