

**MPC 12/17/07 TRSP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



Abbildung ähnlich

Small and medium-sized polycarbonate enclosures  
 The polycarbonate enclosures of the MPC series are ideal for building into electrical, electromechanical and pneumatic devices as well as PCBs. The enclosures are used in situations with extreme mechanical and chemical conditions.

Features:

- 17 sizes in 2 versions
- Grey or transparent cover
- Cover with lead-seal holes
- Mounting holes outside the seal area
- Receptacle threads for rail mounting, mounting plates and circuit board
- Comprehensive accessories
- Weidmüller can manufacture and supply the enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

Version	MPC (polycarbonate empty enclosure), Empty enclosure, Height: 125 mm, Width: 175 mm, Depth: 75 mm, Material: Polycarbonate, Miscellaneous, Light Grey, Transparent
Order No.	<a href="#">9535300000</a>
Type	MPC 12/17/07 TRSP
GTIN (EAN)	4032248009190
Qty.	1 Stück

## MPC 12/17/07 TRSP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	75 mm	Depth (inches)	2.953 inch
Height	125 mm	Height (inches)	4.921 inch
Width	175 mm	Width (inches)	6.89 inch
Net weight	368 g		

### Temperatures

Operating temperature	-50 °C...130 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	130 °C		

### Cable glands, right

M12	6	M16	4
M20	4		

### Cable glands, top/bottom

M12	4	M16	3
M20	3		

### General information

Access opening: height	121.5 mm	Access opening: width	171.5 mm
Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction	Enclosure attachment	Holes 4.5 mm
Flange plate	No	Impact resistance	IK06
Integral fixing	thanks to self-tapping screws	Lid	Yes
Lid attachment	4 polyamide crosshead screws	Material	Polycarbonate
Material thickness	3.5 mm	Number of lid screws	4
Operating temperature, max.	130 °C	Operating temperature, min.	-50 °C
Protection degree	IP66, IP67	Seal material	Polyurethane
Surface finish	Miscellaneous	Torque for lid screws	0.8 Nm

### horizontal assembly

WDU 10 / ZDU 10	1x11	WDU 2,5 / ZDU 2,5 / IDU 2,5	1x22
WDU 4 / ZDU 4	1x19	WDU 6 / ZDU 6	1x14

### vertical assembly

WDU 10 / ZDU 10	1x11	WDU 2,5 / ZDU 2,5 / IDU 2,5	1x22
WDU 4 / ZDU 4	1x19	WDU 6 / ZDU 6	1x14

### Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

## MPC 12/17/07 TRSP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity - MPC Empty Enclosures - DoC DE PS2420 201008 001ISS00</a> <a href="#">EU Declaration of Conformity - Klippon K Terminal Box - DoC DE PS270X 160308 002ISS03</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

MPC 12/17/07 TRSP

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Zeichnungen

[www.weidmueller.com](http://www.weidmueller.com)

