

**VT COMBI PRO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

**General ordering data**

Version	Testing tools, 2-pole voltage tester type 1156
Order No.	<a href="#">9918860000</a>
Type	VT COMBI PRO
GTIN (EAN)	4032248405749
Qty.	1 pc(s).

Creation date February 28, 2023 9:45:49 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## VT COMBI PRO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	67 mm	Depth (inches)	2.638 inch
Height	33 mm	Height (inches)	1.299 inch
Width	264 mm	Width (inches)	10.394 inch
Net weight	356 g		

## Technical data

Description of article	Voltage tester up to 690 V / 100 Hz LED
------------------------	---

## Measuring and testing devices

AC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V	AC voltage measuring range	6-690 V
Battery type	1.5 V type AAA battery	Buzzer	Yes
Continuity test	Yes - visual + acoustic	DC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V
DC voltage measuring range	690 V	Display	LED
Frequency range, max.	400 Hz	Frequency range, min.	16 Hz
Insulation test	8 kV	Load switchable	Yes
Measuring range category	CAT III – 690V/CAT IV – 600V	Note	Screw-on, thicker test probes
One-handed operation	Yes	Peak voltage resistance	8 kV
Phase sequence display	Yes	Protection degree	IP65
RCD circuit breaker	The selectable load enables conscious triggering of a 30 mA RCD circuit breaker	Rated voltage, max.	690 V AC/DC
Rated voltage, min.	6 V	Residual-current test	Yes
Test probe illumination	Yes	Test probe protection GS 38	Yes
Tested and approved according to	IEC 61243-3:2014 (DIN EN 61243-3:2015-08)	Working temperature, max.	55 °C
Working temperature, min.	-15 °C		

## Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ECLASS 9.0	27-20-03-08
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-08
ECLASS 11.0	27-20-03-08	ECLASS 12.0	27-20-03-08

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b05b5122-6117-4cb0-b28c-df32f921fa36

## Approvals

Approvals



ROHS Conform

**VT COMBI PRO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">9918860000_DECLARATION_OF_CONFORMITY.pdf</a>
Product Change Notification	<a href="#">PCN-PW641110-20180410-00-A EN</a> <a href="#">PCN-PW641110-20180410-00-A DE</a>
User Documentation	<a href="#">BANL_manual 2pol Tester</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

---