

Shaft Supports T-Shaped Side Slit (Machined)


Standard / Wide

■Features: Shafts can be secured without damage. Each screw can be fixed from above.

■Standard



RoHS10




Technical drawing showing dimensions: H1, H, E, W, L1, L, d, d2, d1, l, C, T, S, W, L1, d, E, Tightening Screw M, d2, d1, l, C. Includes detail of 2-d Through and 2-d Through, d1 Counterbore Depth l.

⚠ Pilot hole for tapped hole M may be through.


⚠ Slit is machined after the mounting hole D is bored to H7 tolerance. The tolerance may become H8 or so depending on the machining condition.

Part Number		H										Unit Price									
Type	D	Height H Selectable Type										Height H Configurable Type									
Height H Selectable	8	10	15	20	25	30	40	10.0~40.0	44	H+7											
SHWTB	10	15	20	25	30			10.0~30.0	50	H+9											
SHWTM	12	15	20	25	30			15.0~30.0	50	H+10											
SHWTS	13	15	20	25	30			15.0~40.0	50	H+11											
SHWTA	16	15	20	25	30				50	H+12											
Height H Configurable	20	20	25	30	40	50	60	20.0~60.0	75	H+15											
SHWTBH	25	20	25	30	40	50	60		94	H+18											
SHWTMH	30	25	30	40	50	60		25.0~60.0	98	H+21											
SHWTS	35	30	40	50	60				103	H+24											
SHWTA	40	30	40	50	60	80		30.0~80.0	103	H+27											

■Wide



RoHS10



Technical drawing showing dimensions: H1, H, E, W, L1, L, d, d2, d1, l, C, T, S, W, L1, d, E, Tightening Screw M, d2, d1, l, C. Includes detail of 2-d Through, 4-d Through, and 2-d Through, d1 Counterbore Depth l.

⚠ D dimensions 30 ~ 40 come with 2 screws.

⚠ Pilot hole for tapped hole M may be through.

⚠ Slit is machined after the mounting hole D is bored to H7 tolerance. The tolerance may become H8 or so depending on the machining condition.

Part Number		H										Unit Price									
Type	D	Selection										SHWTBN SHWTMN SHWTSN SHWTAN									
SHWTBN	8	10	15	20	25	30	40		62	H+10											
SHWTMN	10	15	20	25	30	40	50	60		H+11											
SHWTSN	12	15	20	25	30	40	50	60		H+12											
SHWTAN	13	15	20	25	30	40	50	60		H+14											
	15	15	20	25	30	40	50	60													
	16	15	20	25	30	40	50	60													
	20	20	25	30	40	50	60	80		H+18											
	25	20	25	30	40	50	60	80		H+21											
	30	25	30	40	50	60	80		102	H+24											
	35	25	30	40	50	60	80		106	H+27											
	40	40	50	60	80				111												

Ordering Example

Part Number - H

SHWTM8 - 25


SHWTMH8 - 25.6

SHWTSN30 - 40

ex

Combination of these app. examples can be selected on our website.

Details about Selection Procedure P.87



Shaft Supports T-Shaped Split (Machined)


Standard / Wide

■Features: Shaft Supports are removable and thus, facilitate maintenance.

■Standard



RoHS10




Technical drawing showing dimensions: H1, H, E, W, L1, L, d, d2, d1, l, C, T, S, W, L1, d, E, Tightening Screw M, d2, d1, l, C. Includes detail of 2-d Through, d1 Counterbore Depth l.


⚠ Pilot hole for tapped hole M may be through.

Part Number		H										Unit Price									
Type	D	Height H Selectable Type										Height H Configurable Type									
Height H Selectable	3	10	15	20				10.0~20.0	38	H+6											
SHPTB	4	10	15	20	25			10.0~25.0	38	H+7											
SHPTM	5	10	15	20	25	30	40	10.0~40.0	50												
SHPTS	6	10	15	20	25	30	40	10.0~30.0	50	H+10											
SHPTA	8	10	15	20	25	30			60	H+12											
Height H Configurable	12	15	20	25	30			15.0~40.0	60												
SHPTBH	13	15	20	25	30				82	H+17											
SHPTMH	16	15	20	25	30	40		20.0~60.0	82	H+20											
SHPTSH	20	20	25	30	40	50	60	25.0~60.0	110												
SHPTAH	25	25	30	40	50	60		30.0~80.0	116	H+30											
	30	30	40	50	60	80		40.0~80.0	154	H+40											
	40	40	50	60	80																
	50	40	50	60	80																

■Wide



RoHS10



Technical drawing showing dimensions: H1, H, E, W, L1, L, d, d2, d1, l, C, T, S, W, L1, d, E, Tightening Screw M, d2, d1, l, C. Includes detail of 2-d Through, 4-d Through, and 2-d Through, d1 Counterbore Depth l.

⚠ D dimensions 30 ~ 50 come with 4 screws.

⚠ Pilot hole for tapped hole M may be through.

Part Number		H										Unit Price									
Type	D	Selection										SHPTBN SHPTMN SHPTSN SHPTAN									
SHPTBN	8	10	15	20	25	30	40		62	H+10											
SHPTMN	10	15	20	25	30	40	50	60		H+11											
SHPTSN	12	15	20	25	30	40	50	60		H+12											
SHPTAN	13	15	20	25	30	40	50	60		H+14											
	15	15	20	25	30	40	50	60													
	16	15	20	25	30	40	50	60													
	20	20	25	30	40	50	60	80		H+18											
	25	20	25	30	40	50	60	80		H+20											
	30	25	30	40	50	60	80		85	H+24											
	35	25	30	40	50	60	80		110	H+30											
	40	30	40	50	60	80			116	H+40											
	50	40	50	60	80				154												

Ordering Example

Part Number - H

SHPTM8 - 25

SHPTMH8 - 25.6

SHPTMN25 - 40

ex

Combination of these app. examples can be selected on our website.

Details about Selection Procedure P.87

