


Oil Free Bushings
Copper Alloy, Flanged, Standard

Points on Comparing Similar Products | If you use it for high-precision positioning, high load weight, and high frequency movement, consider from the existing product series.

Features: Flanged, less likely to pull-out.

Flanged, Standard



Part Number													Dm6		Thickness (N)	H	0 t-0.1	Housing Dia. (Recommended Dimension)	
Type	dF7		L															Ref. Dim.	Tolerance (H7)
MPFZ	5	+0.032 +0.020	10	12							9	+0.028 +0.019	2	14	2	9	+0.015 0		
	6		10	12	15					10		16		10					
	8	+0.040 +0.025	10	12	15	20	25	30		12	+0.034 +0.023	20		12		+0.018 0			
	10		10	12	15	20	25	30		14		14							
	12	+0.050 +0.032	10	12	15	20	25	30		18	+0.041 +0.028	3	25	3	18	+0.021 0			
	13		10	12	15	20	25	30		19			26		19				
	15		10	12	15	20	25	30		21			28		21				
	16		12	15	20	25	30	35	40	22			29		22				
	18		15	20	25	30	35	40	24	32	24								
	20	+0.061 +0.040	15	20	25	30	35	40	30	+0.050 +0.034	5	40	5	30	+0.025 0				
	25		15	20	25	30	35	40	50			35		45		35			
	30		20	25	30	35	40	50	40			50		40					
	35	+0.075 +0.050	20	25	30	35	40	50	45	60		45							
	40		20	25	30	35	40	50	50	65		50							
	50		30	35	40	50	60	60	+0.060 +0.041	75	60	+0.030 0							

Ordering Example

Part Number - L

MPFZ20 - 30

Part Number		Unit Price									
Type	d	L10	L12	L15	L20	L25	L30	L35	L40	L50	L60
MPFZ	5			-	-	-	-	-	-	-	-
	6				-	-	-	-	-	-	-
	8					-	-	-	-	-	-
	10						-	-	-	-	-
	12							-	-	-	-
	13							-	-	-	-
	15							-	-	-	-
	16	-								-	-
	18	-	-							-	-
	20	-	-							-	-
	25	-	-								-
	30	-	-	-							-
	35	-	-	-							-
	40	-	-	-							-
	50	-	-	-	-	-					-

