

Hinge Plates



Hinge Bolt

-Male Thread Type (R Type, Oil Free Type), Female Thread Type-

CAD Data

CAD Data



A

B

D

E

Mounting Hole Specified Type

Part Number	Shape	DH7	T Selection	1mm Increment		N	F	W	L	C	S	d1	d2	M	Unit Price Qty. 1-9		
				P	Q										HPFB	HPFM	HPFS
HPFB HPFM HPFS	A	10	9	15-30	12-20	12	F=L-N-P-S	32	65	10	8	6	6.5	6	42,30	45,50	64,20
	B	12	12	20-35	20-25	16		38	75	10	8	9	8	45,00	48,40	68,20	
	C	16	16	25-55	20-35	20		50	105	15	10	10	11	10	51,30	54,70	77,30
	D	20	-	-	-	-		-	-	-	-	-	-	-	56,30	59,70	84,70

Mounting Hole Fixed Type



Part Number	Shape	DH7	T	P	Q	N	F	W	L	C	d1	d2	M	Unit Price Qty. 1-9		
														HPACM	HPACN	HPAN
HPACM	A	16	10	30	30	25	40	50	105	15	10	-	10	19,80		
HPACN	B	-	-	-	-	-	-	-	-	-	-	-	-	18,00		
HPAN	E	-	-	-	-	-	-	-	-	-	-	-	-	9,80		

Order Example Part Number: HPFB B 12 - 9 - 25 - 25 Days to Ship: 10 Days Price: 5,00 EUR/piece Express A P.92

Alterations Part Number: HPE12 - 100 - 16 - CC10 Price: 2,00

Volume Discount P.92

Quantity	1-9	10-29	30-49	50-99
Rate	Price List	5%	10%	15%



Economy Type  **HPE** 

Part Number	Type	D	L 10mm Increment	T Selection	R	H	Unit Price Qty. 1-4		
							HPFB	HPFM	HPFS
HPE	A	8	40-100	9 12 15 16	11	22	4,80		
		10					5,80		
		12					7,80		
		16					7,80		
		20					9,80		

Order Example Part Number: HPE12 - 100 - 16 Days to Ship: 8 Days Price: 3,00 EUR/piece Express A P.92

Volume Discount P.92

Quantity	1-4	5-9	10-19	20-29
Rate	Price List	5%	10%	15%

Joint Plate  **JNPB** 

Part Number	Type	A	B	T	JNPB	JNPS	Unit Price Qty. 1-4				
							HPFB	HPFM	HPFS		
JNPB JNPS	A	30	10 20	2.0	2.0	5	2,70	4,40	3,60	5,00	
							2,90	4,60	3,80	5,10	
							3,10	4,80	3,90	5,30	
							3,20	4,90	4,10	5,40	
							3,40	5,10	4,20	5,60	
		60	10 20 30 40 50	4.5	4.0	10	6	3,60	5,30	4,40	5,80
								3,70	5,40	4,60	5,80
								3,80	5,50	4,60	6,00


Order Example Part Number: JNPB50 - 30 - 2.0 Days to Ship: 8 Days Price: 3,00 EUR/piece Express A P.92

Volume Discount P.92

Quantity	1-4	5-9	10-19	20-49
Rate	Price List	5%	10%	15%

Male Thread

Male Thread				Female Thread				Material	Surface Treatment
Standard Type		R Type		Oil Free Type		R Type			
Right-Hand Thread	Left-Hand Thread	Right-Hand Thread	Left-Hand Thread	Right-Hand Thread	Left-Hand Thread	Right-Hand Thread	Left-Hand Thread		
HGBB	HGBBL	HGBBR	HGBBRL	HGMBB	HGKBB	HGKBL	HGKBL	1.1191/C45E	Black Oxide
HGBM	HGBML	HGBMR	HGBMRL	HGMBM	HGKBM	HGKBM	HGKBM	1.4301/X5CrNi18-10	Electroless Nickel Plating
HGBS	HGBSL	HGBSR	HGBSRL	HGMBM	HGKS	HGKSL	HGKSL		

Male Thread Standard Type 

Male Thread R Type 