
Support Units - Fixed Side, Square < Convenient>

Type with Damper / Type with Dowel Holes

Support Units with Damper integrate the Stopper for Ball Screws and the Support Unit and are suitable for use in limited spaces.



M12x1.0


M15x1.0

15

12 7 15.5

Take care in combining No.20 with Ball Screw BSSZ (K) 2510, BSSR (K) 2510 or BSST2510. The ball screw nut may come in contact with the bottom surfaces

MISUMI Original Standard Type with Dowel Holes achieves better repeatability and accurate positioning than conventional products.





BSWD

Features of Support Units with Dowel Holes

There is a method of pressing against vertical dowel pins for locating support units. However, care is required when tightening the mounting screws

so as not to cause clearances between the pins and the support unit.

Using the Support Units with Dowel Holes reduces the assembling time as troublesome adjustments for the clearance will not be needed any more.




When tightening the mounting screws, clearance between the pins and the wall may be created. If this clearance exists readjustment is required.




As the dowel holes are provided with the Support Units locating is easy.

Support Units - Support Side, Square < Convenient>

Type with Damper / Type with Retaining Ring



Part Number		ч	- 1	В	н	h	B ₁	H ₁	D	v	d1	Damper Dimension					Bearing	Retaining	Unit Price
Type	No.	а	-	В	-	"	ы	-	F		ui	а	b	С	r	t	Type	Ring	1 ~ 10 pc (s).
BUND	1022	8	20	70	40	22		21	52	22 26 32	9	34	10	6	12	10	B608ZZ	STWN8	
	10				43	25	36	24				34							
	1223	10 20			41	23	30	22				46	12	7	15.5		B6000ZZ	STWN10	
	12				43	25		24				40	12						
	1526				46	26	8 41	21	60		11		15	10	18		B6002ZZ	STWN15	
	1528				48	28		23				50							
	15				50	*30		25											
	20	20	26	95	58	30	56	30		47		60	19	10	25		B6204ZZ	STWN20	
	25	25	30	105	68	35	66	25	85	52	1	80	19	15	28		B6205ZZ	STWN25	



Part Number														Retaining Ring				BTN	BTNM
Type No.		d	L	В	Н	h	B ₁	H ₁	P	٧	d ₁	d2	l	G	Retaining	Bearing Type	Retaining Ring	Unit Price	Unit Price
Type	NO.													u	Ring	Type	Tillig	1 ~ 10 pc (s).	1 ~ 10 pc (s).
BTN BTNM	6	6	12	42	25	13	18	20	30	⊣ 17	5.5	9.5	11	3	RTWN, S17	B606ZZ	STWN, S6		
	8	١٥	15	52	32	17	25	26	38		6.6	11	11	3					
	10	8		70	43	25	36	24	52	22	9			3	RTWN, S22	B608ZZ	STWN, S8		
	12	10	20							26				3	RTWN, S26	B6000ZZ	STWN, S10		
	15	15		80	80 50		41	25	60	32	11	-	-	4	RTWN, S32	B6002ZZ	STWN, S15		
	20	20	20 26 95		58	*30	56	30	75	47				4.5	RTWN, S47	B6204ZZ	STWN, S20		
	25	25	30	105	68	35	66	25	85	52				4.5	RTWN, S52	B6205ZZ	STWN, S25		

* Take care in combining No.20 with Ball Screw BSSZ(K)2510, BSSR(K)2510 or BSST2510. The ball screw nut may come in contact with the bottom surfaces.



- Part Number 🍸 For details of Bearings in addition to mounting interface accuracies of Support Units, Included Collar and Bearing Nut, see 壓 P.759
 - TBC Plating products are filled with low dust generation grease for cleanrooms.
 - The store Accessories with care since they are required when assembling.