


Slide Blocks

■ **Features:** Used in combination with L-Gibs (P.656,657). Different assemblies are possible by alterations.



Part Number	1mm Increment				
SLI SLD	A	B	C	T	L
SLI	50~150	20~80	5~60	5~20	50~150

<Machining Conditions>
5 ≤ B-T ≤ 60
20 ≤ A-2C
When C > 15, L ≤ 100

Ordering Example: Part Number - A - B - C - T - L
SLI - A120 - B50 - C20 - T10 - L100

Part Number	A	L	B	Unit Price															
				20~30		31~40		41~50		51~60		61~70		71~80					
				SLI	SLD	SLI	SLD	SLI	SLD	SLI	SLD	SLI	SLD	SLI	SLD				
SLI	50~80	50~80	81~100																
	81~100																		
	101~130																		
	131~150																		
SLD	50~80	81~100	101~130																
	81~100																		
	101~130																		
	131~150																		

■ Machining Limits (Distance between Holes, Thickness between Holes and Edges)

Alterations: Part Number - A - B - C - T - L - (SS, SQ...etc.)
SLI - A120 - B50 - C20 - T10 - L100 - SS15-M5

Tapped Hole Dia. b (Min. Value)	
3, 4, 5	0.8
6, 8, 10	1.0

Alterations	Tapped Hole Machining				Groove Machining
	1 Tapped Hole on the side	4 Tapped Holes on the side	2 Tapped Holes on the top	4 Tapped Holes on the top	
Code	SS	SQ	JD	JQ	TM
Spec.	SS=1mm Increment Ordering Code: SS8-M5 ■ Tapped Hole Dia. Selection Dimension: 3 4 5 6 8 10	SQ, Y, G=1mm Increment Ordering Code: SQ12-Y15-G10-M5 ■ Tapped Hole Dia. Selection Dimension: 3 4 5 6 8 10	JD, Y, G=1mm Increment Ordering Code: JD40-Y12-G30-M8 ■ Tapped Hole Dia. Selection Dimension: 3 4 5 6 8 10	JQ, F, Y, G=1mm Increment Ordering Code: JQ15-F20-Y12-G50-M6 ■ Tapped Hole Dia. Selection Dimension: 3 4 5 6 8 10	TM, F=1mm Increment Ordering Code: TM-F10 Groove Depth 1.5mm 2 ≤ TM, F TM+F ≤ (A/2)-2


② 2 types or more of alterations cannot be used in combination.

Oil Free Slide Plates

Copper Alloy (Upper-Lower Surface Ground)

■ **Features:** Maintenance-free and economical Slide Plates.

① For material characteristic values, refer to P.380. ② Initial greasing is recommended for effective use.



Part Number	Type	w	L	Mounting Hole Qty.	Hole Position	X	ℓ1	Y	ℓ2	Unit Price					
										STRL	STRLU	STRLUP	STRLT		
STRL (Plate Thickness 10mm)	Single Row	20	*30	1	-	-	-	-	-						
			*40	2	10	20	-	-	-						
			*50	2	10	30	-	-	-						
			*60	2	10	40	-	-	-						
			80	2	10	60	-	-	-						
			100	3	10	40	-	-	-						
			120	3	10	50	-	-	-						
			150	3	10	65	-	-	-						
			200	4	10	60	-	-	-						
			250	5	13	56	-	-	-						
			300	5	14	68	-	-	-						
			STRLU (Plate Thickness 5mm)	Single Row	20	*30	1	-	-	-	-	-			
*40	2	10				20	-	-	-						
*50	2	10				30	-	-	-						
*60	2	10				40	-	-	-						
80	2	10				60	-	-	-						
100	3	10				40	-	-	-						
120	3	10				50	-	-	-						
150	3	10				65	-	-	-						
200	4	10				60	-	-	-						
250	5	13				56	-	-	-						
300	5	14				68	-	-	-						
STRLUP (Plate Thickness 5mm) (Counterbored) (W20 only)	Single Row	20				40	1	-	-	-	-	-			
			60	2	10	40	-	-	-						
			80	2	10	60	-	-	-						
			100	3	12	38	-	-	-						
			120	3	12	48	-	-	-						
			150	3	12	63	-	-	-						
			200	4	13	58	-	-	-						
			250	5	13	56	-	-	-						
			300	5	14	68	-	-	-						
			STRLT (Plate Thickness 3mm) (* marked sizes only)	Double Row	20	80	4	10	60	20	40				
						100	4	13	74	20	40				
						120	6	13	47	20	40				
150	6	13				62	20	40							
200	6	13				87	20	40							
250	8	14				74	20	40							
300	10	14				68	20	40							

Hole Machining Details																										
STRL (Hex Socket Extra Low Head Cap Screw)	<table border="1"> <thead> <tr> <th>w</th> <th>d</th> <th>d1</th> <th>t</th> <th>Included Screw Size</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>4.5</td> <td>8</td> <td>4</td> <td>M4-20</td> </tr> <tr> <td>30</td> <td>5.5</td> <td>9.5</td> <td>5</td> <td>M5-20</td> </tr> <tr> <td>40</td> <td>6.5</td> <td>11</td> <td>6</td> <td>M6-20</td> </tr> <tr> <td>50</td> <td>9</td> <td>15</td> <td>6</td> <td>M8-20</td> </tr> </tbody> </table>	w	d	d1	t	Included Screw Size	20	4.5	8	4	M4-20	30	5.5	9.5	5	M5-20	40	6.5	11	6	M6-20	50	9	15	6	M8-20
w	d	d1	t	Included Screw Size																						
20	4.5	8	4	M4-20																						
30	5.5	9.5	5	M5-20																						
40	6.5	11	6	M6-20																						
50	9	15	6	M8-20																						
STRLU (Hex Socket Flat Head Cap Screw)	<table border="1"> <thead> <tr> <th>w</th> <th>d</th> <th>d1</th> <th>t</th> <th>Included Screw Size</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>4.5</td> <td>9.5</td> <td>2.5</td> <td>M4-20</td> </tr> <tr> <td>30</td> <td>5.5</td> <td>11.1</td> <td>2.8</td> <td>M5-20</td> </tr> <tr> <td>40</td> <td>6.5</td> <td>13.1</td> <td>3.3</td> <td>M6-20</td> </tr> <tr> <td>50</td> <td>9</td> <td>17.6</td> <td>4.3</td> <td>M8-20</td> </tr> </tbody> </table>	w	d	d1	t	Included Screw Size	20	4.5	9.5	2.5	M4-20	30	5.5	11.1	2.8	M5-20	40	6.5	13.1	3.3	M6-20	50	9	17.6	4.3	M8-20
w	d	d1	t	Included Screw Size																						
20	4.5	9.5	2.5	M4-20																						
30	5.5	11.1	2.8	M5-20																						
40	6.5	13.1	3.3	M6-20																						
50	9	17.6	4.3	M8-20																						
STRLUP (Hex Socket Extra Low Head Cap Screw)	<table border="1"> <thead> <tr> <th>w</th> <th>d</th> <th>d1</th> <th>t</th> <th>Included Screw Size</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>4.5</td> <td>8</td> <td>3</td> <td>M4-10</td> </tr> </tbody> </table>	w	d	d1	t	Included Screw Size	20	4.5	8	3	M4-10															
w	d	d1	t	Included Screw Size																						
20	4.5	8	3	M4-10																						
STRLT (Hex Socket Flat Head Cap Screw)	<table border="1"> <thead> <tr> <th>w</th> <th>d</th> <th>d1</th> <th>t</th> <th>Included Screw Size</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>4.5</td> <td>9.5</td> <td>2.5</td> <td>M4-20</td> </tr> <tr> <td>30</td> <td>5.5</td> <td>11.1</td> <td>2.8</td> <td>M5-20</td> </tr> <tr> <td>40</td> <td>6.5</td> <td>13.1</td> <td>3.3</td> <td>M6-20</td> </tr> </tbody> </table>	w	d	d1	t	Included Screw Size	20	4.5	9.5	2.5	M4-20	30	5.5	11.1	2.8	M5-20	40	6.5	13.1	3.3	M6-20					
w	d	d1	t	Included Screw Size																						
20	4.5	9.5	2.5	M4-20																						
30	5.5	11.1	2.8	M5-20																						
40	6.5	13.1	3.3	M6-20																						

① Initial greasing is recommended for effective use.

Ordering Example: Part Number - L
STRLU30 - 150
STRLT20 - 60

① STRLUP is applicable to W dimension 20mm only.
② Only * marked L dimensions are available for STRLT.