

Roller Conveyors - Overview

Unit Price = Body Price + Shape Charge								
Part Number	Body Price			Config. Price (Body Price +)				
Type	D	60-200	201-400	401-550	A	D	E	G
HRD	6						-	
	8						-	
	12						-	
HRDB	6						-	
	8						-	
	12						-	
HRDM	6						-	
	8						-	
	12						-	
HRDS	6						-	
	8						-	
	12						-	

* Holes for Roller Shafts are provided at 50mm pitch on Ø38 x P100 flames.