

Resin Roller Conveyor Length Configurable

Roller Diameter 20mm, 30mm, 50mm Type



■Features: Light weight (approx. 2.3kg/m) Roller Conveyor composed of resin rollers and aluminum frame.



RoHS 10

Type	①Roller (HRJA) M Material	Bearing M Material	②Frame M Material	S Surface Treatment
ROCOP	ABS Plastic	Outer Wheel / Inner Wheel : Polyacetal Retainer : Nylon 66 Cover : ABS Plastic Ball : EN 1.4301 Equiv.	Aluminum	Clear Anodize

Type	R Pin M Material	S Surface Treatment	Frame Coupling Support M Material	S Surface Treatment	Screw, Nut M Material	S Surface Treatment
ROCOP	Steel	Trivalent Chromate	Steel	Trivalent Chromate	Steel	Trivalent Chromate



For Alterations, see P.1170. For Frame Side View, see P.1166.

Part Number Type	D	Number of Rollers	W (Roller Width)	P (Pitch)	A	D ₁	t	H	Roller Strength for Reference (N)				
									W113	W213	W313	W413	W513
ROCOP	20	5~40	113	25	6	9.5	1.5	62	113	105	98	90	83
	30	5~32	213	40	8	14	1.8	67	162	154	147	139	132
	50	5~26	313	50									
	50	5~13	413	75	12	17	2.8	66.5	314	304	294	289	279
	50	5~13	513	100									

■Roller Diameter 20, 30mm Type

Part Number Type	Number of Rollers	L			Unit Price 1 ~ 5 pc(s).											
					W113			W213			W313			W413		
		D20 P=25	D30 P=40	D30 P=50	D20 P=25	D30 P=40	D30 P=50	D20 P=25	D30 P=40	D30 P=50	D20 P=25	D30 P=40	D30 P=50	D20 P=25	D30 P=40	D30 P=50
ROCOP	5	(120)	(195)	(245)												
	6	(145)	(235)	(295)												
	7	(170)	(275)	(345)												
	8	(195)	(315)	(395)												
	9	(220)	(355)	(445)												
	10	(245)	(395)	(495)												
	11	(270)	(435)	(545)												
	12	(295)	(475)	(595)												
	13	(320)	(515)	(645)												
	14	(345)	(555)	(695)												
	15	(370)	(595)	(745)												
	16	(395)	(635)	(795)												
	17	(420)	(675)	(845)												
	18	(445)	(715)	(895)												
	19	(470)	(755)	(945)												
	20	(495)	(795)	(995)												
	21	(520)	(835)	(1045)												
	22	(545)	(875)	(1095)												
	23	(570)	(915)	(1145)												
	24	(595)	(955)	(1195)												
	25	(620)	(995)	(1245)												
	26	(645)	(1035)	(1295)												
	27	(670)	(1075)	-												
	28	(695)	(1115)	-												
	29	(720)	(1155)	-												
	30	(745)	(1195)	-												
	31	(770)	(1235)	-												
	32	(795)	(1275)	-												
	33	(820)	-	-												
	34	(845)	-	-												
	35	(870)	-	-												
	36	(895)	-	-												
	37	(920)	-	-												
	38	(945)	-	-												
	39	(970)	-	-												
	40	(995)	-	-												

■Roller Diameter 50mm Type

Part Number Type	Number of Rollers	L		Unit Price 1 ~ 5 pc(s).							
				W113		W213		W313		W413	
		P=75	P=100	P=75	P=100	P=75	P=100	P=75	P=100	P=75	P=100
ROCOP	5	(370)	(495)								
	6	(445)	(595)								
	7	(520)	(695)								
	8	(595)	(795)								
	9	(670)	(895)								
	10	(745)	(995)								
	11	(820)	(1095)								
	12	(895)	(1195)								
	13	(970)	(1295)								

 Ordering Example

Part Number - Number of Rollers - W - P

ROCOP20 - 10 - 213 - 25

For orders larger than indicated quantity, please check with WOS.

For orders larger than indicated quantity, please check with WOS.


 Alterations

P.1170

Roller Conveyor Length Configurable

Roller 19mm Diameter Type



■Features: Short roller conveyors 1m or less, with configurable width and length.



RoHS 10

Roller Pitch P=20	P=30	①Roller (HRO19) M Material	S Surface Treatment	Bearing M Material	②Frame M Material	S Surface Treatment
ROCO	ROCON	Steel	Trivalent Chromate	Steel	Steel	Trivalent Chromate

Roller Pitch P=20	P=30	R Pin M Material	S Surface Treatment	Frame Coupling Support M Material	S Surface Treatment	Screw, Nut M Material	S Surface Treatment
ROCO	ROCON	Steel	Trivalent Chromate	Steel	Trivalent Chromate	Steel	Trivalent Chromate



For Alterations, see P.1170. For Frame Side View, see P.1166.

Part Number Type	Number of Rollers	(L)		Unit Price									
		ROCO P=20	ROCON P=30	ROCO (P=20)					ROCON (P=30)				
		W113	W213	W313	W413	W513	W113	W213	W313	W413	W513	W113	W213
ROCO ROCON	6	(120)	(190)										
	7	(140)	(200)										
	8	(160)	(230)										
	9	(180)	(260)										
	10	(200)	(290)										
	11	(220)	(330)										
	12	(240)	(360)										
	13	(260)	(390)										
	14	(280)	(430)										
	15	(300)	(460)										
	16	(320)	(490)										
	17	(340)	(500)										
	18	(360)	(530)										
	19	(380)	(560)										
	20	(400)	(590)										
	21	(420)	(630)										
	22	(440)	(660)										
	23	(460)	(690)										
	24	(480)	(730)										
	25	(500)	(760)										
	26	(520)	(790)										
	27	(540)	(800)										
	28	(560)	(830)										
	29	(580)	(860)										
	30	(600)	(890)										
	31	(620)	(930)										
	32	(640)	-										
	33	(660)	-										
	34	(680)	-										
	35	(700)	-										
	36	(720)	-										
	37	(740)	-										
	38	(760)	-										
	39	(780)	-										
	40	(800)	-										
	41	(820)	-										
	42	(840)	-										
	43	(860)	-										
	44	(880)	-										
	45	(900)	-										
	46	(920)	-										
	47	(940)	-										
	48	(960)	-										

 Ordering Example

Part Number - W

ROCO38 - 113

ROCON22 - 313

 Alterations

P.1170