

Roller Conveyors - Overview

Unit Price = Body Price + Shape Charge									
Part Number		Body Price			Config. Price (Body Price +)				
Type	D	60-200	201-400	401-550	A	D	E	G	
HRD	6						-		
	8						-		
	12						-		
HRDB	6						-		
	8						-		
	12						-		
HRDM	6						-		
	8						-		
	12						-		
HRDS	6						-		
	8						-		
	12						-		

Type	Material	Surface Treatment	Bearing
CNMR	Steel	Trivalent Chromate Plating	Machined Bearing
CNMRC		Hard Chrome Plating	
CNMRS	Stainless Steel	-	

B=15, 25

B=50, 100

Part Number		B	d	d1	W	Allowable Load (N)	Unit Price		
Type	D						CNMR	CNMRC	CNMRS
CNMR CNMRC CNMRS	20	15	6.1	10	17	294			
		25	6.1						
		50	6.2			-	-		
		100	6.2			-	-		

Type	ROCO		ROCON		ROCOM		ROCOG		ROCOE ROCOJ		ROCOH	
Frame Size	Ø19xP20		Ø19xP30		Ø28xP30		Ø28xP50		Ø38xP50 Ø38xP100*		Ø38xP75	
(L)	F	G	F	G	F	G	F	G	F	G	F	G
100~199	10	20	20	35	-	-	-	-	-	-	-	-
200~299		40	10	55	25	70						
300~399		80	15	90	15	90	150	150	150	150	150	
400~499			20	155	20	155						25
500~599			10	145	25	160	150	150	150	150	150	
600~699			15	150	15	150						150
700~799			20	155	20	155	150	150	150	150	150	
800~899			10	145	25	160						150
900~1000			15	150	15	150	150	150	150	150	150	

* Holes for Roller Shafts are provided at 50mm pitch on Ø38 x P100 flames.