


Adjusting Bolts


Adjusting Bolts



RoHS 10

Thread	Type	M Material	S Surface Treatment
Coarse	AJST	EN 1.1191 Equiv.	Black Oxide
	AJSTM	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTS	EN 1.4301 Equiv.	-
Fine	AJSTF	EN 1.1191 Equiv.	Black Oxide
	AJSTMF	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTFS	EN 1.4301 Equiv.	-

Refer to the price list for applicable M size.




25/(1.5/)


Part Number		L 5mm Increment	d	T	MxPitch		B	D	C	E	Unit Price					
Type	M				Fine	Coarse					Coarse			Fine		
											AJST	AJSTM	AJSTS	AJSTF	AJSTMF	AJSTFS
(Coarse) AJST AJSTM AJSTS	3	10~45	2.5	7	-	3x0.5	3	4.5	5	6				-	-	-
	4	10~60	3.5		4x0.5	4x0.7		5.5		7						
	5	10~70	4.5		5x0.5	5x0.8		7.5		8						
	6	15~80	5.5		6x0.75	6x1.0		8.5		10						
(Fine) AJSTF AJSTMF AJSTFS	8	20~100	7.5	12	8x0.75	8x1.25	6	11.5	15	13						
	10	25~100	9.5	16	10x1.0	10x1.5	7	15.5		17						
	12	25~150	11.5	19	12x1.0	12x1.75	8	17.5		19		-	-	-	-	-
	16	25~150	15.5		-	16x2.0		21.5		24		-	-	-	-	

Ordering Example Part Number - L
AJST8 - 25

Example Combination of these app. examples can be selected on the Web.
Details about Selection Procedure [P.87](#)
For Blocks for Adjusting Bolts, see [P.1729](#).
e-Catalog Search Keyword #MA221 Search
* Enter the search keyword in the search box on e-Catalog.
The search result will be shown in "Modular Assembler" area.




Adjusting Bolt - T Compact



RoHS 10

Thread	Type	M Material	S Surface Treatment
Coarse	AJSTC	EN 1.1191 Equiv.	Black Oxide
	AJSTCM	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTCS	EN 1.4301 Equiv.	-
Fine	AJSTCF	EN 1.1191 Equiv.	Black Oxide
	AJSTCMF	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTCFS	EN 1.4301 Equiv.	-

Applicable block for Adjusting Bolts to T Compact Type is T Compact, Side Mounting Type ([P.1729](#)).




25/(1.5/)


Part Number		L 5mm Increment	d	T	MxPitch		B	D	C	E	Unit Price					
Type	M				Fine	Coarse					Coarse			Fine		
											AJSTC	AJSTCM	AJSTCS	AJSTCF	AJSTCMF	AJSTCFS
(Coarse) AJSTC AJSTCM AJSTCS	4	10~60	3.5	3	4x0.5	4x0.7	3	5.5	5	7						
	5	10~70	4.5	5	5x0.5	5x0.8	4.6	7.5	10	8						
	(Fine) AJSTCF AJSTCMF AJSTCFS	6	15~80		5.5	6x0.75		6x1.0	8.5	10						
	8	20~100	7.5		8x0.75	8x1.25	6	11.5	15	13						

Ordering Example Part Number - L
AJSTC8 - 25

Example Adjusting Bolt (AJSTC)
For Adjusting Bolt Block (AJSCC [P.1729](#))




Adjusting Bolts - Hex Socket



RoHS 10

Thread	Type	M Material	S Surface Treatment
Coarse	AJSTR	EN 1.1191 Equiv.	Black Oxide
	AJSTMTR	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTRS	EN 1.4301 Equiv.	-



The directions of the outer hex head E and the hex socket E1 are not equal.

Part Number	Type	M	L 5mm Increment	d	T	MxPitch		B	D	C	E	E1	ℓ	Unit Price		
						Coarse	Fine							AJSTR	AJSTMTR	AJSTRS
AJSTR	AJSTMTR	4	10~50	3.5	7	4x0.7	3	5.5	7	2.5	2.5					
		5	10~50	4.5	9	5x0.8	4.6	7.5	10	8	3					
		6	15~50	5.5	9	6x1.0	6	8.5	10	10	4					
		8	20~50	7.5	12	8x1.25	6	11.5	15	13	5					

Ordering Example Part Number - L
AJSTR4 - 20


Adjusting Bolts - Hex Socket Knurled Knobs



RoHS 10

Thread	Type	M Material	S Surface Treatment
Coarse	AJKTN	EN 1.1191 Equiv.	Black Oxide
	AJKTNM	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJKTNS	EN 1.4301 Equiv.	-
Fine	AJKTNF	EN 1.1191 Equiv.	Black Oxide
	AJKTNMF	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJKTNMF	EN 1.4301 Equiv.	-

Refer to the price list for applicable M size.



25/(1.5/)

Part Number		L 5mm Increment		d	T	MxPitch		B	D	A	F	E2	ℓ	Unit Price				
Type	M					Fine	Coarse							Coarse		Fine		
(Coarse) AJKTN AJKTNM AJKTNS	3	10~45	2.5	7	-	3x0.5	3	4.5	7	10	5	4						
	4	10~60	3.5	7	4x0.5	4x0.7	3	5.5	7	10	5	4						
	5	10~70	4.5	9	5x0.5	5x0.8	4.6	7.5	15	15	8	7						
	6	15~80	5.5	9	6x0.75	6x1.0	4.6	8.5	15	15	8	7						
	8	20~100	7.5	12	8x0.75	8x1.25	6	11.5	25	20	10	9						
(Fine) AJKTNF AJKTNMF	10	25~100	9.5	16	10x1.0	10x1.5	7	15.5	25	20	10	9						
	12	25~150	11.5	19	12x1.0	12x1.75	8	17.5	25	20	10	9						
	16	25~150	15.5	19	-	16x2.0	8	21.5	25	24	10	9						


Ordering Example Part Number - L
AJKTN10 - 80

Adjusting Bolts - Knurled Knobs



RoHS 10

Thread	Type	M Material	S Surface Treatment
Coarse	AJSTK	EN 1.1191 Equiv.	Black Oxide
	AJSTKM	EN 1.1191 Equiv.	Electroless Nickel Plating
	AJSTKS	EN 1.4301 Equiv.	-



25/(1.5/)

Part Number	Type	M (Coarse)	L 5mm Increment	d	T	B	D	A	F	Unit Price		
										AJSTK	AJSTKM	AJSTKS
AJSTK	AJSTKM	3	10~20	2.5	7	3	4.5	4	16			
		4	10~30	3.5	7	3	5.5	4	16			
		5	10~40	4.5	9	4.6	7.5	6	20			
		6	15~50	5.5	9	4.6	8.5	6	20			
		8	20~50	7.5	12	6	11.5	6	20			

Ordering Example Part Number - L
AJSTK4 - 25