

Components for Inspection

Components for Inspection and Locating Kits, Construction Balls, Pads, Covers

■ Features: For locating removable jig parts. (See app. example below)


Components for Inspection and Locating Kits

RoHS10





Config.	Type	Material, Hardness, Surface Treatment	
		Collar / Bushing	Stripper Bolt
Provided	Hex Socket Head With Wing Screw	KJLP	EN 1.7220 Equiv. 33-38HRC
Not Provided	Hex Socket Head With Wing Screw	KJLPC KJLPN KJLPNC	EN 1.0038 Equiv. Trivalent Chromate 45-50HRC

* If only shoulder bolts for wrench are required, order GMSB (P. 2-216).



■ Bushing
* Tolerance is applicable only with no Knurling.



Part Number		L	I.D. / Screw			Stripper Bolt			Unit Price			
Type	D		P	M	f	Length	Head	Wing Screw	KJLP	KJLPC	KJLPN	KJLPNC
KJLP	KJLPC	12	15	6	4	7	30	4	9	3	15	21
KJLPN	KJLPNC	20	25	6	4	7	40	4	9	3	15	21
			15	10	8	12	25	8	16	6	24	31
			30	10	8	12	40	8	16	6	24	31


■ Ordering Example: KJLP20 - 15

■ Alterations: KJLP20 - 15 - (HT, STC)

Alterations		Code	Spec.
Flats Machining	HT	Chamfers a side of collar and bushing.	
Additional Surface Treatment (Black Oxide)	STC	Adds black oxide surface treatment. Applicable to collar and bushing only.	

Construction Balls

CRB




■ Material: EN 1.4125 Equiv.

■ Hardness: HRC56

Pads for Construction Balls

CRBP




■ Material: EN 1.0038 Equiv.

■ Surface Treatment: Black Oxide

Covers for Construction Balls

CRBC



■ Material: EN 1.0330 Equiv.

■ Surface Treatment: Black Oxide

RoHS10


Components for Inspection

Pin Clips, Wires for Pins, Chains for Pins


■ Features: For storing slot pins when not in use.

Pin Clips

CLIP8



CLIP16




■ Material: EN 1.4319 Equiv.

Part Number		Applicable Slot Pin Handle Dia.	Unit Price	Volume Discount Rate	
Type	No.	1 ~ 9 pc(s).	10 ~ 29 pcs.	30 ~ 49 pcs.	50-100 pcs.
CLIP	8	Ø8, 10, 12			
	16	Ø16, 20, 25			

■ Ordering Example: CLIP8
■ Part Number: CLIP8
■ For orders larger than indicated quantity, please request a quotation.




For storing slot pins when not in use.



Clamping force may be adjusted slightly by tightening the mounting screw.

Wires for Slot Pins

KJW



RoHS10

■ Material: EN 1.4301 Equiv.

■ KJWB




Part Number		L 50mm Increment	Applicable Screw	Unit Price	
Type	D			KJW	KJWB
KJW	1	300~700	M5		
KJWB	2	300~700	M5		

* D=2 product is shipped if D dimension isn't specified.

* The thickness of KJWB is D (wire dia.) + approx. 0.5mm of vinyl coating thickness.

Chains for Slot Pins

KJWCH



■ Material: Ring: EN 1.4301 Equiv.

Others: JIS-SWRM

■ Surface Treatment: Nickel Plating

Part Number		A	B	C	R	Applicable Slot Pin Handle Dia.	Unit Price
Type	No.						
KJWCH	1	14	2	5	7	8, 10	
	2	17	4	6	8.5	12	
	3	21	6	7	10.5	16	
	4	25	8	8	12.5	20	
	5	30	10	9	15	25	
	6	36	12	10	18	30	

■ Ordering Example: KJW2 - 350

■ Part Number: KJW2 - 350

■ Part Number: KJWCH3