


One End Tapped / One End Threaded



- One End Threaded



RoHS10

One End Tapped EN 1.0038 Equiv.	One End Threaded EN 1.0038 Equiv.
NLMN	NLON
LSMN	LSON
PLMN	PLON
EN 1.4301 Equiv.	EN 1.4301 Equiv.
SLMN	SLON




L Dimension Tolerance
L 8~300 ± 0.1
L300.5~600 ± 0.3
L600.5~800 ± 0.4

However, when $L \leq 200$, and when order volume at one time is less than 10 pcs., since the processing is done simultaneously, the difference of L dimension is within ± 0.02 .
 ❗ Except L Dimension Selectable



Example



Attachment Block for Hex Posts HXTM

Next Page




A diagram of a cylinder with a rectangular flange on the left. A dimension line below the cylinder indicates its length is L_{KC} .





Part Number		Unit Price			
Type	B	Min. L ~ 200	L200.5~400	L400.5~600	L600.5~800
EN 1.0038 Equiv. NLON	5		-	-	-
	6		-	-	-
	7		-	-	-
	8			-	-
	10			-	-
	12			-	-
	13			-	-
	14				-
	17				-
	19				-
	24				-
	27				
	30				
32					
EN 1.0038 Equiv. Black Oxide LSON	5		-	-	-
	6		-	-	-
	7		-	-	-
	8			-	-
	10			-	-
	12			-	-
	13			-	-
	14				-
	17				-
	19				-
	24				-
	27				
	30				
32					
EN 1.0038 Equiv. Electroless Nickel Plating PLON	5		-	-	-
	6		-	-	-
	7		-	-	-
	8			-	-
	10			-	-
	12			-	-
	13			-	-
	14				-
	17				-
	19				-
	24				-
	27				
	30				
32					
EN 1.4301 Equiv. SLON	5		-	-	-
	6		-	-	-
	7		-	-	-
	8			-	-
	10			-	-
	12			-	-
	13			-	-
	14				-
	17				-
	19				-
	24				-
	27				
	30				
32					

Side Tapped



⚠ B dimension corresponds to B dim. of Hex Posts.



Ordering Example **Part Number**
HXSM14