

# Toggle Clamps

## Hold Down, Horizontal Standard Handle (Flange Base)




■ Features: MC01-2B is the size between MC01-2 and MC01-3.

1N=0.101972kgf


Part Number	MC01-1	MC01-S1
Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.
Surface Treatment	Trivalent Chromate	-
Tightening Force (N)	264.6	-
Weight (g)	30	-
Arm Open-Close Angle	90°	-
Handle Open-Close Angle	75°	-
Accessory	* Nylon Bolt	Stainless Steel Bolt
Unit Price		






Part Number	MC01-2	MC01-S2
Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.
Surface Treatment	Trivalent Chromate	-
Tightening Force (N)	264.6	-
Weight (g)	35	-
Arm Open-Close Angle	90°	-
Handle Open-Close Angle	75°	-
Accessory	* Nylon Bolt	Stainless Steel Bolt
Unit Price		



Part Number	MC01-2B
Body Material	EN 1.0038 Equiv.
Surface Treatment	Trivalent Chromate
Tightening Force (N)	400
Weight (g)	60
Arm Open-Close Angle	90°
Handle Open-Close Angle	75°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	



Part Number	MC01-3	MC01-S3
Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.
Surface Treatment	Trivalent Chromate	-
Tightening Force (N)	882	-
Weight (g)	130	-
Arm Open-Close Angle	85°	-
Handle Open-Close Angle	73°	-
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70	* Stainless Steel Bolt
Unit Price		



Ordering Example  
Part Number  
**MC01-1**

# Toggle Clamps

## Hold Down, Horizontal Standard Handle (Flange Base) / High Arm Type (Flange Base)



■ Features: MC01-10 is larger than MC01-4 in size and clamping force. High Arm Type with an arm position higher than conventional products is adjustable without spacers.  
(MC01H-3: 16mm higher than MC01-3; MC01H-4: 19mm higher than MC01-4)

1N=0.101972kgf

Part Number	MC01-4	MC01-S4
Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.
Surface Treatment	Trivalent Chromate	-
Tightening Force (N)	2352	-
Weight (g)	265	-
Arm Open-Close Angle	90°	-
Handle Open-Close Angle	65°	-
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70	* Stainless Steel Bolt
Unit Price		





Part Number	MC01-10
Body Material	EN 1.0038 Equiv.
Surface Treatment	Trivalent Chromate
Tightening Force (N)	3400
Weight (g)	640
Arm Open-Close Angle	90°
Handle Open-Close Angle	68°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	



Part Number	MC01H-3
Body Material	EN 1.0038 Equiv.
Surface Treatment	Trivalent Chromate
Tightening Force (N)	900
Weight (g)	150
Arm Open-Close Angle	85°
Handle Open-Close Angle	73°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	



Part Number	MC01H-4
Body Material	EN 1.0038 Equiv.
Surface Treatment	Trivalent Chromate
Tightening Force (N)	2270
Weight (g)	290
Arm Open-Close Angle	90°
Handle Open-Close Angle	65°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	



Ordering Example  
Part Number  
**MC01-10**  
**MC01H-3**

