


Toggle Clamps


Side Push-Pull Free Mounting Direction / Horizontal (Flange Base)


Toggle Clamps


Hold Down, Vertical Handle (Flange Base)

1N=0.101972kgf


Side Push-Pull Free Mounting Direction		Part Number	MC02-1	MC02-S1	Side Push-Pull Free Mounting Direction		Part Number	MC02-2	MC02-S2	Side Push-Pull Free Mounting Direction		Part Number	MC02-3
		Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv. Shaft Material: EN 1.4005 Equiv. Pin: EN 1.4006 Equiv.			Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv. Shaft Material: EN 1.4005 Equiv. Pin: EN 1.4006 Equiv.			Body Material	EN 1.0038 Equiv.
Surface Treatment		* Trivalent Chromate		-	Surface Treatment		* Trivalent Chromate		-	Surface Treatment		* Trivalent Chromate	
Stroke (mm)		20.34		-	Stroke (mm)		40		-	Stroke (mm)		66.7	
Tightening Force (N)		900		-	Tightening Force (N)		1470		-	Tightening Force (N)		3138	
Handle Open-Close Angle		180°		-	Handle Open-Close Angle		180°		-	Handle Open-Close Angle		180°	
Weight (g)		120		-	Weight (g)		280		-	Weight (g)		750	
Accessory		Steel Bolt		Stainless Steel Bolt	Accessory		Steel Bolt		Stainless Steel Bolt	Accessory		Steel Bolt	
Unit Price					Unit Price					Unit Price			




Horizontal (Flange Base)		Part Number	MC03-1	MC03-S1	Horizontal (Flange Base)		Part Number	MC03-2	MC03-3
		Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.			Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.
Surface Treatment		* Trivalent Chromate		-	Surface Treatment		* Trivalent Chromate		-
Stroke (mm)		17		-	Stroke (mm)		16		-
Tightening Force (N)		450		-	Tightening Force (N)		500		-
Handle Open-Close Angle		190°		-	Handle Open-Close Angle		180°		-
Weight (g)		50		-	Weight (g)		65		-
Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70		* Stainless Steel Bolt	Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70		* Stainless Steel Bolt
Unit Price					Unit Price				




Ordering Example
Part Number
MC02-1




1N=0.101972kgf

Hold Down, Vertical Handle (Flange Base)		Part Number	MC04-1	MC04-S1	Hold Down, Vertical Handle (Flange Base)		Part Number	MC04-2	MC04-S2	Hold Down, Vertical Handle, Welded Tip (Flanged Base)		Part Number	MC04-5
		Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.			Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.			Body Material	EN 1.0038 Equiv.
Surface Treatment		* Trivalent Chromate		-	Surface Treatment		* Trivalent Chromate		-	Surface Treatment		* Trivalent Chromate	
Tightening Force (N)		441		-	Tightening Force (N)		882		-	Tightening Force (N)		2270	
Weight (g)		60		-	Weight (g)		170		-	Weight (g)		340	
Arm Open-Close Angle		100°		-	Arm Open-Close Angle		95°		-	Arm Open-Close Angle		100°	
Handle Open-Close Angle		56°		-	Handle Open-Close Angle		60°		-	Handle Open-Close Angle		56°	
Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70		* Stainless Steel Bolt	Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70		* Stainless Steel Bolt	Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70	
Unit Price					Unit Price					Unit Price			



Hold Down, Vertical Handle (Flange Base)		Part Number	MC04-3	MC04-S3	Hold Down, Vertical Handle (Flange Base)		Part Number	MC04-4
		Body Material	EN 1.0038 Equiv.	EN 1.4301 Equiv.			Body Material	EN 1.0038 Equiv.
Surface Treatment		* Trivalent Chromate		-	Surface Treatment		Trivalent Chromate	
Tightening Force (N)		2205		-	Tightening Force (N)		3332	
Weight (g)		355		-	Weight (g)		635	
Arm Open-Close Angle		100°		-	Arm Open-Close Angle		112°	
Handle Open-Close Angle		56°		-	Handle Open-Close Angle		61°	
Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70		* Stainless Steel Bolt	Accessory		Bolt with Rubber Material: NBR Hardness: Shore A70	
Unit Price					Unit Price			



Ordering Example
Part Number
MC04-1