

Standard / Dimension Configurable

	Type			Material	Color
	Pkg.	Dimension Selectable	Dimension Configurable		
	PACK-WSJJ	WSJJ	FWSJJ	Polyacetal	White
	-	WSJK	FWSJK		Black
	PACK-WSJM	WSJM	FWSJM	MC Nylon Standard Grade	Blue
	-	WSJW	FWSJW		Ivory
	-	WSJD	FWSJD	MC Nylon Conductive Grade	CDR2
	-	WSJT	FWSJT		CDR6
	-	WSJB	FWSJB	Bakelite	Paper Base
	-	WSJN	FWSJN		Cloth Base
	-	WSJF	FWSJF	Fluororesin	Natural Color
	-	WSJP	FWSJP		Natural Color
	-	WSJE	FWSJE	PEEK	White
	-				Gray
	-			Epoxy Glass	Green
	-				
	-				

Part Number		V Selection	T Selection	PACK-WSJJ				PACK-WSJM			
				Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type	D			1 ~ 4 pkg(s).	5~9	10~19	20~30	1 ~ 4 pkg(s).	5~9	10~19	20~30
PACK-WSJJ PACK-WSJM	4	2	2								
	5	2 3	2								
	6	2 3 4	2								
	8	3 4 5 6	2 3 5								
	10	3 4 5 6 8	2 3 5								
	12	4 5 6 8	2 3								
	15	6 8 10 12	2 3								
20	6 8 10 12	2 3 5									

 **Ordering Example**

• Sold by the package

Part Number	-	V	-	T
PACK-WSJJ4	-	2	-	2

Part Number		V Selection	T Selection	Unit Price								
Type	D			WSJJ WSJK	WSJM WSJW	WSJD	WSJT	WSJB	WSJN	WSJF	WSJP	WSJE
WSJJ WSJK WSJM WSJW WSJD WSJT WSJB WSJN WSJF WSJP WSJE	4	2	2									
	5	2 3	2									
	6	2 3 4	2									
	8	2 3 4 5 6	2 3 5									
	10	2 3 4 5 6 8	2 3 5									
	12	3 4 5 6 8 10	2 3 5									
	13	4 5 6 8 10	2 3 5									
	14	4 5 6 8 10	2 3 5									
	15	4 5 6 8 10 12	2 3 5									
	16	4 5 6 8 10 12	2 3 5									
	20	4 5 6 8 10 12 15 16	2 3 5									
	25	6 8 10 12 15 16 20	2 3 5									
	30	8 10 12 15 16 20 25	2 3 5									
	35	10 12 15 16 20 25	3 5 10									
	40	10 12 15 16 20 25 30	3 5 10									
	50	10 12 15 16 20 25 30	3 5 10									
60	15 16 20 25 30	3 5 10			-		-	-	-			

Part Number	D	V	T	Unit Price								
		0.5mm Increment (V3 or More)	0.5mm Increment	FWSJJ FWSJK	FWSJM FWSJW	FWSJD	FWSJT	FWSJB	FWSJN	FWSJF	FWSJP	FWSJE
FWSJJ FWSJK FWSJM FWSJW FWSJD FWSJT FWSJB FWSJN FWSJF FWSJP FWSJE	4.0~10 (0.5mm Increment)	0 (No Hole Machining) 2.0 2.6 3.0~58.0 (V≤D-2) 58.5~90.0 (V≤D-6)	2.0~ 5.0									
			5.5~10									
	10.5~20 (0.5mm Increment)		2.0~ 5.0									
			5.5~10									
	21~30 (1mm Increment)		2.0~ 5.0									
			5.5~10									
	31~40 (1mm Increment)		2.0~ 5.0									
			5.5~10									
	41~50 (1mm Increment)		2.0~ 5.0									
			5.5~10									
	51~60 (1mm Increment)		2.0~ 5.0				-			-	-	-
			5.5~10				-			-	-	-
	61~80 (1mm Increment)		2.0~ 5.0				-			-	-	-
			5.5~10				-			-	-	-
	81~100 (1mm Increment)		2.0~ 5.0				-			-	-	-
			5.5~10				-			-	-	-

Alterations  Part Number - D - V - T - (VKC, TKC)
 WSJJ6 - 4 - 2 - VKC
 FWSJM - D10 - V4 - T2 - TKC

	I.D. Tolerance Change	Thickness Tolerance Change
Alterations		
Code	VKC	TKC
Spec.	Changes the I.D. tolerance to $^{+0.1}_0$. ORDERING CODE VKC - When $D \leq 50$, $D-V \geq 6$ - When $51 \leq D \leq 80$, $D-V \geq 10$ - When $81 \leq D \leq 100$, $D-V \geq 16$	Changes the Thickness Tolerance to ± 0.05. ORDERING CODE TKC - When $D \leq 50$, $D-V \geq 6$ - When $D \leq 80$, $D-V \geq 10$ - When $D \leq 100$, $D-V \geq 16$