

Device Stands
Round Flanged, Through Holes

Features: A set of a post and stand for mounting a round flanged type device.

Sets (Posts + Brackets)

Sets (Posts + Brackets)



Table with columns: Type (Round Flanged, Solid, Hollow), Post (Material, Hardness, Surface Treatment), Bracket (Material, Surface Treatment), and Accessory (Solid, Hollow). Rows include CSTN, MCSTN, SCSTN, CSTNM, MCSTNM, SCSTNM and their hollow counterparts.

Bracket only



Table with columns: Type (No Dowel Hole, With Dowel Holes), Material, Surface Treatment, and Accessory (No Dowel Hole, With Dowel Holes). Rows include CSTF, CSTFM, CSPF, and CSPTF.

* Case Induction Hardened(Post): 58HRC ~, Depth 1.0 ~ 1.5
* There may be no electroless nickel plating at ends and grooves of posts.
* For Hex Socket Head Cap Screws, a black oxide bracket matches a black oxide screw, and an electroless nickel plating bracket matches a trivalent chromate screw.

Sets (Posts + Brackets)



Bracket only



Bracket only



RoHS10

Main product specification table with columns: Part Number, Type, L (mm), A, D1, H, T, l, P.C.D., K, J, M, (d), Bracket with Dowel Holes, and Included Hex Socket Head Cap Screw. Rows list various part numbers and their specifications.

Ordering Example: Part Number - L, MCSPN50 - 500, CSTF20

Round Flanged Set

Table showing Round Flanged Set specifications with columns D, L, and Unit Price for Solid and Hollow types across various dimensions.

Round Flanged with Dowel Holes Set

Table showing Round Flanged with Dowel Holes Set specifications with columns D, L, and Unit Price for Solid type across various dimensions.

Bracket only

Table showing Bracket only specifications with columns DH7, Tolerance, and Unit Price for CSTF, CSTFM, and CSPF types across various dimensions.

Alterations, Part Number, L, (BH), CSTN15, 150, BH

Table with columns: Alterations, Code, and Spec. It details mounting hole enlargements and includes a table for included washers (WSSB and WSSM series).