


Square Shims

For Motor Base / For Pillow Block

Square Shim Package / Square Shims (Adjustment)

For Motor Base / For Pillow Block

■ For Motor Base
■ For Pillow Block



Type		Material	Hardness	Thickness (T) Tolerance				
For Motor Base	For Pillow Block			0.05	0.1	0.2	0.5	1.0
CIMMS	CIMSS	EN 1.4301 Equiv.	370~430HV	±0.005	±0.02	±0.03	±0.04	±0.05
CIMMB	CIMSB	Brass (EN CW505L Equiv. or EN CW507L Equiv.)	-	±0.005	±0.02	±0.03	±0.05	±0.08
CIMM	CIMSN	EN 1.0330 Equiv.	-	-	±0.03	±0.03	±0.06	±0.11

4-R1 (For Motor Base)

4-R1 (For Pillow Block)
UCPA, UCUP, UCP

4-R1 (For Pillow Block)
PBT, PBR, PBRs

6.3/6.3

■ For Motor Base


Part Number		T Selection	A	C	Q	Unit Price												
Type	No.					CIMMS					CIMMB					CIMM		
						T0.05	T0.1	T0.2	T0.5	T1.0	T0.05	T0.1	T0.2	T0.5	T1.0	T0.1	T0.2	T0.5
CIMMS CIMMB CIMM	1035	(0.05) For CIMMB and CIMMS only	10	5	3.5				-	-	-	-	-	-	-	-	-	-
	1245		12	6	4.5				-	-	-	-	-	-	-	-	-	-
	1455		14	7	5.5				-	-	-	-	-	-	-	-	-	-
	1665		16	8	6.5				-	-	-	-	-	-	-	-	-	-
	2009		20	10	9													
	3013		30	15	13													
	4312		43	22	12													
	4814		48	24	14													
	5314		53	27	14													
	6816		68	34	16													
	8320		83	42	20													
	9825		98	49	25													
	11830		118	54	30													
	20036		200	100	36													

■ For Pillow Block

Part Number		T Selection	A	B	C	Q	D	E	Applicable Pillow Block	Unit Price																
Type	No.									CIMSS					CIMSB					CIMSN						
										T0.05	T0.1	T0.2	T0.5	T1.0	T0.05	T0.1	T0.2	T0.5	T1.0	T0.1	T0.2	T0.5	T1.0			
CIMSS CIMSB CIMSN	10	(0.05) For CIMSS and CIMSB only	16	17.5	10.5	7	7	2	PBT10, PBR10, PBRs10							-	-	-	-	-	-	-	-	-	-	
	12		16	18	10.5	7	7	2.5	PBT12, PBR12, PBRs12							-	-	-	-	-	-	-	-	-	-	
	15		16	20	11.5	7	7	2.5	PBT15, PBR15, PBRs15							-	-	-	-	-	-	-	-	-	-	
	17		18	21	12	7	8	2.5	PBT17, PBR17, PBRs17							-	-	-	-	-	-	-	-	-	-	
	20		20	24.5	14.5	10	10	3	PBT20, PBR20, PBRs20							-	-	-	-	-	-	-	-	-	-	
	25		20	27.5	16.5	10	10	3	PBT25, PBR25, PBRs25							-	-	-	-	-	-	-	-	-	-	
	30		26	33	20	13	13	4	PBT30, PBR30, PBRs30							-	-	-	-	-	-	-	-	-	-	
	204A		40	27	15	13	-	-	UCPA204 UCUP204																	
	205A		45	30	16	13	-	-	UCPA205 UCUP205																	
	206A		50	36	22	17	-	-	UCPA206 UCUP206																	
	207A		55	41	26	17	-	-	UCPA207 UCUP207																	
	208A		58	41	25	17	-	-	UCPA208 UCUP208																	
	204		38	42	26	13	-	-	UCP-204																	
	205		38	42	25	13	-	-	UCP-205																	
	206		48	54	32	17	-	-	UCP-206																	
	207		48	54	34	17	-	-	UCP-207																	
	208		54	58	35	17	-	-	UCP-208																	
	209		54	60	38	17	-	-	UCP-209																	
	210		60	65	42	20	-	-	UCP-210																	

Ordering Example
Part Number - T
CIMM2009 - 0.5
CIMSN204A - 0.1

■ Sold by the package
(1 pack=10 pcs.)



Type		Material	Hardness	Thickness (T) Tolerance				
For Motor Base	For Pillow Block			0.05	0.1	0.2	0.5	1.0
PACK-CIMMS	PACK-CIMSS	EN 1.4301 Equiv.	370~430HV	±0.005	±0.02	±0.03	±0.04	±0.05

4-R1 (For Motor Base)

4-R1 (For Pillow Block)
UCPA, UCUP, UCP

4-R1 (For Pillow Block)
PBT, PBR, PBRs

6.3/6.3


■ For Motor Base / For Pillow Block Sold by the package 1 package contains 10 pieces.

Part Number		T Selection	A	B	C	Q	D	E	Unit Price				
Type	No.								T0.05	T0.1	T0.2	T0.5	T1.0
For Motor Base (EN 1.4301 Equiv.) PACK-CIMMS	1035	0.05	10	-	5	3.5	-	-	-	-	-	-	-
	1245		12	-	6	4.5	-	-	-	-	-	-	-
	1455		14	-	7	5.5	-	-	-	-	-	-	-
	1665		16	-	8	6.5	-	-	-	-	-	-	-
	2009		20	-	10	9	-	-	-	-	-	-	-
	3013		30	-	15	13	-	-	-	-	-	-	-
	4312		43	-	22	12	-	-	-	-	-	-	-
	4814		48	-	24	14	-	-	-	-	-	-	-
	5314		53	-	27	14	-	-	-	-	-	-	-
	6816		68	-	34	16	-	-	-	-	-	-	-
	8320		83	-	42	20	-	-	-	-	-	-	-
	9825		98	-	49	25	-	-	-	-	-	-	-
For Pillow Block (EN 1.4301 Equiv.) PACK-CIMSS	10		16	17.5	10.5	7	7	2	-	-	-	-	-
	12		16	18	10.5	7	7	2.5	-	-	-	-	-
	15		16	20	11.5	7	7	2.5	-	-	-	-	-
	17		18	21	12	7	8	2.5	-	-	-	-	-
	20		20	24.5	14.5	10	10	3	-	-	-	-	-
	25		20	27.5	16.5	10	10	3	-	-	-	-	-
	30		26	33	20	13	13	4	-	-	-	-	-
	204A		40	27	15	13	-	-	-	-	-	-	-
	205A		45	30	16	13	-	-	-	-	-	-	-
	206A		50	36	22	17	-	-	-	-	-	-	-
	207A		55	41	26	17	-	-	-	-	-	-	-
	208A		58	41	25	17	-	-	-	-	-	-	-
	204		38	42	26	13	-	-	-	-	-	-	-
	205		38	42	25	13	-	-	-	-	-	-	-
	206		48	54	32	17	-	-	-	-	-	-	-
	207		48	54	34	17	-	-	-	-	-	-	-
	208		54	58	35	17	-	-	-	-	-	-	-
	209		54	60	38	17	-	-	-	-	-	-	-
	210		60	65	42	20	-	-	-	-	-	-	-

Ordering Example
Part Number - T
PACK-CIMMS2009 - 0.5
PACK-CIMSS204A - 0.1

Please specify number of packages to order.
Quantity 1 means one package.

■ Adjustment Type



Type		Material	Surface Treatment	Hardness	Thickness (T) Tolerance	
One Slot	Two Slots				0.5	1.0
ASA	ASF	EN 1.0330 Equiv.	Black Oxide	-	±0.05	±0.1
ASAS	-	EN 1.4301 Equiv.	-	370~430HV	±0.05	±0.1

One Slot

Two Slots

6.3/6.3

Part Number		No.	A	C	Q	ASA				ASAS			
Type	T					T0.5	T1.0	T0.5	T1.0	T0.5	T1.0	T0.5	T1.0
ASA ASAS	0.5 1.0	1035	10	5	3.5	-	-	-	-	-	-	-	-
		1245	12	6	4.5	-	-	-	-	-	-	-	-
		1455	14	7	5.5	-	-	-	-	-	-	-	-
		1665	16	8	6.5	-	-	-	-	-	-	-	-
		2009	20	10	9	-	-	-	-	-	-	-	-

Part Number		T	P	L	Unit Price		Volume Discount Rate
Type	No.				1 ~ 49 pc(s)	50 ~ 100	
ASF	0.5	30	50	60	-	-	-
		40	60	70	-	-	-
		50	70	80	-	-	-
		60	80	90	-	-	-

For orders larger than indicated quantity, please check with WOS.

Ordering Example
Part Number - No.
ASA0.5 - 1035
Part Number - P
ASF0.5 - 30