

Wires / Connecting Parts

Wires

LPWW

A Shape

B Shape

C Shape

RoHS10

Dimension in () is for reference only.

Material: EN 1.4301 Equiv.

Part Number	Shape	L 50mm Increment	Allowable Load (Ref.)	Unit Price
Type	Shape			A B C
LPWW	A B C	100~500	9kg	
		550~1000		

Part Number

Type Shape L

LPWW C 850

Wires

Loop Dia. Configurable

CWAB

CWCB (Nylon Coating)

CWAC

CWCC (Nylon Coating)

RoHS10

Wire Material: EN 1.4301 Equiv.

Ordering Example

Part Number

Type Y Selection L

CWAB 10 500

CWCC 20 850

Alterations

Part Number L DW(TKC) DW(TKC)

CWAB10 500 DW3

CWAC15 800 DW5

CWCC20 850 DW4 TKC

Bracket on Looped Part

Shipped with bracket set on the looped part. One metal joint for CWAB and CWCB and one or two joint(s) for CWAC and CWCC are selectable.

Applicable only to CWAB, CWCB, CWAC, CWCC.

Spec.

Mounting Bracket TKC (P276)

Retainer Washer DW (P276)

Material: EN 1.4301 Equiv.

Accessory: Flat Head Screw M4-5, 2 pcs. (EN 1.4301 Equiv.)

Swage TKC with wire threaded.

Swage DW with its 0a part wire threaded.

Code

TKC DW

Retainer Washers

DW

Registered Utility Model Registration No.3167276

Material: EN 1.4301 Equiv.

Part Number	Nominal	d	D	P	a	A	t	Unit Price	Volume Discount Rate
Type								1 ~ 9 pc(s).	10 ~ 49 pcs.
DW	3	3.2	7	5	2	4	0.5		
	4	4.3	10	6.3	2.5	5	0.8		
	5	5.5	12	8	3	6	1		
	6	6.5	13	9.4	3.5	8	1.5		

For orders larger than indicated quantity, please check with WOS.

Example

Screw DW5

Washer

CBSTS5-10

KJPSHZ

Ordering Example

Part Number

DW4

Mounting Brackets

TKC

2-M4 Countersink

Material: EN 1.4301 Equiv.

Accessory: Flat Head Screw M4-5, 2 pcs. (EN 1.4301 Equiv.)

Part Number	Mass	Applied Load	Unit Price	Volume Discount Rate
Type			1 ~ 19 pc(s).	20 ~ 49 pcs.
TKC	7g	20kg		

The reference applied load is only a guideline.

Ordering Example

Part Number

TKC

Crimp Brackets (Package)

PACK-WW

7±0.4

Material: EN 1.4301 Equiv.

Crimping tool for wires (left-hand page).

Part Number	Unit Price	Volume Discount Rate
Type	No.	1 ~ 2 pkg(s).
PACK-WW	1	

Available for Nylon Coating Type.

Crimping Tools

WWN

Material Special Alloy Steel (Head) / SS41 (Handle) Hardness 60 ~ 65HRC (Blade) / 40 ~ 45HRC (Clamping Part)

RoHS10

Tool for swaging wires (left-hand page) with crimp bracket (PACK-WW1).

Part Number	Unit Price	Volume Discount Rate
Type	1 ~ 2 pc(s).	3 ~ 10 pcs.
WWN		

Attachment for Anchoring Wire

UKC1 UKC2

Material: EN 1.4301 Equiv.

Part Number	Mass	Applicable Wire Dia.	Unit Price	Volume Discount Rate
Type	No.		1 ~ 4 pc(s).	5 ~ 9 pcs.
UKC	1	4g		
	2	9g		

Ordering Example

Part Number

PACK-WW1 WWN UKC1