


Cover Screws

Phillips / Long Knurled Head / Knurled Head



RoHS10

GUTBJ



M (Coarse)

Reference Tensile Breaking Load (N)

M3	1390
M5	4300

* The above data are for reference, not guaranteed.

Material: EN 1.4301 Equiv.


Part Number		M	ℓ	L	A	E	d	Unit Price	Volume Discount Rate
Type									
GUTBJ	3	3	2	5 8 10	6.9	1.9	2.2		
			3.5	6 8 10					
			4	8 10 12					
	4	3	3	6 8 10 12 16	9.4	2.5	3		
			5	10 16					
			6	8 10 12					
	5	3	4	12 16 20	11.8	3.1	3.9		
			6	10 12 16 20					
			8	12 16 20 25 30					
	6	3	5	16	17.8	4.8	6.3		
			10						
			40						

For orders larger than indicated quantity, please check with WOS.



RoHS10

GUTBR



M (Coarse)

Material: EN 1.4305 Equiv.


Part Number		M	ℓ	L	D	A	d	Unit Price	Volume Discount Rate
Type									
GUTBR	3	3	2	6 8 10 12	5.5	10	2.2		
			3.5	6 8 10 12					
			4	8 10 12					
	4	3	3	6 8 10 12 16	7	16	3		
			5	10 12 16					
			6	12 16 20					
	5	3	4	8 10 12 16 20	8.5	20	3.9		
			6	12 16 20					
			8	10 12 16 20 25					
	6	3	5	10 12 16 20	10	30	4.5		
			10	20 25 30					
			13						

For orders larger than indicated quantity, please check with WOS.



RoHS10

RNCB



M

Material: EN 1.4305 Equiv.

Part Number		M	ℓ	L	A	d1	d2	E	Unit Price	Volume Discount Rate
Type										
RNCB	3	3	2	4 6 8 10	12	2.2	6	2.5		
			3.5	6 8 10 12 15						
			4	8 10 12 15 20						
	4	3	3	6 8 10 12 15	16	3	8	3.5		
			5	10 12 15 20						
			6	8 10 12 15						
	5	3	4	12 15 20 25	20	3.9	10	4		
			6	12 15						
			8	15 20						
	6	3	5		24	4.5	12	5		
			10							
			16							

For orders larger than indicated quantity, please check with WOS.



Ordering Example

Part Number - ℓ - L

GUTBJ3 - 4 - 8

GUTBR4 - 5 - 16

RNCB4 - 5 - 16


Cover Screws

Configurable Length



RoHS10

Configurable Length Hex Socket Head




M

Type	Material	Surface Treatment	Strength Class
FGUTM	EN 1.7220 Equiv.	Electroless Nickel Plating	8.8 Equiv.
FGUTS	EN 1.4301 Equiv.	-	A2-70 Equiv.



RoHS10

Configurable Length Knurled




M

Type	Material
FRNCS	EN 1.4305 Equiv.



RoHS10

Configurable Length Button Head Cap



M

Type	Material	Strength Class
FCBBS	EN 1.4301 Equiv.	A2-50 Equiv.

Part Number		1mm Increment							Unit Price			
Type	M	ℓ			L			ℓ・L Machining Conditions	FGUTM	FGUTS	FRNCS	FCBBS
		FGUTM FGUTS	FRNCS	FCBBS	FGUTM FGUTS	FRNCS	FCBBS					
FGUTM FGUTS FRNCS FCBBS	3	2~18	5~16	5~20	4~20	6~20	6~25	ℓ≤L 				
	4	3~18	5~16	5~25	6~20	6~20	6~30					
	5	3~23	5~20	5~25	8~25	8~25	8~30					
	6	4~28	8~20	8~30	8~30	8~25	8~35					
	8	5~38	10~20	10~45	8~40	10~25	10~50					

M	A	A1	A2	E	E1	E2 (Max.)	B	B2	C (Min.)	d	d2
3	5.5	12	5.5	3	2.5	1.6	2.5	2	1.04	2.2	6
4	7	16	7.5	4	3.5	2.2	3	2.5	1.3	3	8
5	8.5	20	9.5	5	4	2.7	4	3	1.56	3.9	10
6	10	24	10.5	6	5	3.3	5	4	2.08	4.5	12
8	13	30	14	8	6	4.4	6	5	2.6	6.3	16



Ordering Example

Part Number - ℓ - L

FRNCS6 - 8 - 20