


Scale Plates / Pointer Plates

* Use as measuring tool for adjustment of machines and equipment.

Scale Plates / Pointer Plates



Use the scale as a reference only.

RoHS 10

Horizontal Scale Type

Width	Type			Material
	Zero at Left	Zero at Right	Center Divided	
8mm	MEPLH	MEPRH	MEPCH	EN AW-1050 Equiv. (Clear Anodize)
12mm	MEPL	MEPR	MEPC MES	
8mm	MEPLSH	MEPRSH	MEPCSH	EN 1.4301 Equiv.
12mm	MEPLS	MEPRS	MEPCS	
12mm	MEPLP	MEPRP	MEPCP	


For adhesive tapes, NITTO500 is used.

Vertical Scale Type


Width	Type			Material
	Zero at Bottom	Center Divided		
15mm	MEPCTT	MEPCT		EN AW-1050 Equiv. (Clear Anodize)
	-	MEPCTP		

8mm Width EN AW-1050 Equiv. are all printed in black. (For EN 1.4301 Equiv., 0 and numbers in 50 increment are printed in red.)


MEPLH (EN AW-1050 Equiv., Clear Anodize) with adhesive tape



MEPLSH (EN 1.4301 Equiv.) Ø3.5x2 places with mounting holes



MEPRH (EN AW-1050 Equiv., Clear Anodize) with adhesive tape



MEPRSH (EN 1.4301 Equiv.) Ø3.5x2 places with mounting holes



MEPCH (EN AW-1050 Equiv., Clear Anodize) with adhesive tape




MEPCSH (EN 1.4301 Equiv.) Ø3.5x2 places with mounting holes




12mm Width (0 and numbers in 50 increment are printed in red.)

MEPL (EN AW-1050 Equiv., Clear Anodize) with adhesive tape



MEPLP (PET Plastic) with adhesive tape

MEPLS (EN 1.4301 Equiv.) Ø3.5x2 places with mounting holes



MEPR (EN AW-1050 Equiv., Clear Anodize) with adhesive tape



MEPRP (PET Plastic) with adhesive tape

MEPRS (EN 1.4301 Equiv.) Ø3.5x2 places with mounting holes



MEPC (EN AW-1050 Equiv., Clear Anodize T0.5) with adhesive tape




MEPCP (PET Plastic T0.2) with adhesive tape

MEPCS (EN 1.4301 Equiv. T0.5) Ø3.5x2 places with mounting holes



Vertical Scale Type (0 and numbers in 50 increment are printed in red.)

MEPCTT (JIS-EN AW-1050 Equiv., Clear Anodize, Vertical) with adhesive tape



MEPCT (JIS-EN AW-1050 Equiv., Clear Anodize, Vertical) with adhesive tape



MEPCTP (PET Plastic, Vertical) with adhesive tape



MES and PET plastic types can be used on curved surfaces.

Hole drilling marks are not printed on PET plastic type of width 8mm.

Double-sided adhesive tape is not attached to Stainless Steel Type. Use the two Ø3.5x2 screw mounting holes.

LC alteration on Stainless Steel Type results in removal of the mounting holes on the ends. Combination with alteration HC is recommended.

Scale Plates Width 12mm Zero at Left/Right

Zero Point Position	Part Number		Unit Price 1 ~ 19 pc(s).	Volume Discount Rate		
	Type	L		20~29	30~49	50~100
Left End	MEPL	100				
		200				
		300				
		600				
	MEPLS	100				
Right End	MEPR	100				
		200				
		300				
		600				
	MEPRS	100				

L600 comes as a set of 2 pcs. of 0 ~ 300 and 301 ~ 600. For orders larger than indicated quantity, please check with WOS.

Scale Plates Width 12mm Center Divided Type

Zero Point Position	Part Number		Unit Price 1 ~ 19 pc(s).	Volume Discount Rate		
	Type	L		20~29	30~49	50~100
Center	MEPC	300				
	MEPCS					
	MEPCP					
	MES					

For orders larger than indicated quantity, please check with WOS.



Part Number - (LC·HC)
MEPL - LC55
MEPLS - LC155-HC

Alterations	Code	Spec.
Hole Machining	HC	Adds mounting holes at hole machining marks. PPS12, PPL20: Ø2.5x2 places MEPL Type/MEPR Type/ MEPC Type/MES/MEPCT ...Hole machining Ø3.5 x 2 areas Not applicable to PET Plastic Type of 8mm width (EN AW-1050 Equiv.). LC≥20 For over L300, adds mounting holes at 2 places for 0 ~ 300, at 2 places for 301 ~ For using combination with LC over L300, hole machining is only applicable to LC≥320.

Scale Plates Width 15mm Vertical Type

Zero Point Position	Part Number		Unit Price 1 ~ 19 pc(s).	Volume Discount Rate		
	Type	L		20~29	30~49	50~100
Bottom	MEPCTT	100				
		200				
		300				
Center	MEPCT	300				
	MEPCTP					

For orders larger than indicated quantity, please check with WOS.

Scale Plates Width 8mm Type

Zero Point Position	Part Number		Unit Price 1 ~ 19 pc(s).	Volume Discount Rate		
	Type	L		20~29	30~49	50~100
Left End	MEPLH	100				
	MEPLSH					
	MEPRH					
Right End	MEPRSH	200				
	MEPCH	300				
Center	MEPCSH					

For orders larger than indicated quantity, please check with WOS.



Part Number
MEPL-200

Alterations	Code	Spec.
Length Cut	LC	Cuts the length in 1mm increment. Specify LC after checking the desired scale range. Cuts the whole length to the specified length. Zero Point Position Applicable Part Number Point of Origin Left End MEPL Type From Zero Point Right End MEPL Type From Zero Point Bottom MEPCTT From Zero Point Center Divided (Only even numbers can be designated) Center MEPCT Type MES From Zero Point Center Divided (Only even numbers can be designated) Not available for PET Plastic Type. LC≥20 There will be two pieces for sizes over 301mm. Mounting hole marks will remain on Stainless Type when cut 5mm from overall length. If the scale plate has a mounting hole originally, the hole may disappear or become semicircular depending on the LC length.

Pointer Plates		PPS12	PPSP12	PPPL	PPPS
Type	Material	Tape			
PPS PPL	EN AW-1050 Equiv. (Clear Anodize)	Attached			
PPSP PPLP	PET Plastic	Attached			
PPPS PPPL	Polycarbonate	Not attached			

Pointer Plates

Part Number		Unit Price 1 ~ 4 pc(s).	Volume Discount Rate		
Type	No.		5~9	10~29	30~100
PPS	12				
PPL	20				
PPPS	30				
PPPL	30				



Part Number - HC
PPS12 - HC

Alterations	Code	Spec.
Hole Machining	HC	Adds mounting holes at hole machining marks. PPS12, PPL20: Ø2.5x2 places Not applicable to PET Plastic Type.