

Trims

Corner Trims

Trims are available in 1m increment. Please note that ordering 5 pieces of L=100 means 5 rolls of 100 meter type.



Color - Pattern Samples

TR_T



(Black - Extra Fine)
B-5

TRCS



(White - Extra Fine)
W-5



(Gray - Wave)
G-6



(Black - Wave)
B-6

Material Properties

Item	TPE	Silicon Rubber
Specific Gravity	0.95	1.2
Heat Resistance	+135°C	+200°C
Low Temp. Resistance	-60°C	-60°C
Compression Set	15~25%	16%


⚠️ TPE does not produce dioxin when burned.

Features

Because of the internal metal strip, it does not require adhesives to install.

Type	Material	
	Main Body	Internal Metal Strip
TR□T	Thermoplastic Elastomer (TPE)	Aluminum
TRCS	Silicon Rubber	EN 1.0330 Equiv.

Applicable Plate Thickness



Bending Directions



Part Number	T	Color - Pattern	L	A	B	W	t	Minimum Bending Radius mm			Applicable Plate Thickness (T Range)		
Type								Bending Directions ①	Bending Directions ②	Bending Directions ③			
TRAT	0.4	B-5	L1~L100 (1m Increment)	4.4	9.7	0.4	1.9	30	30	20	0.3~0.8		
	0.8			4.8	9.5	0.8					0.7~1.2		
	1.6			5.6	9.1	1.6					1.2~1.6		
	2.4			6.4	8.9	2.4					2.0~2.4		
TRBT	0.8	B-5 W-5		5.6	11.3	0.8	2.3	40	40	20	0.6~1.2		
	1.6			6.4	11.1	1.6					1.2~2.0		
	2.4			7.2	11.0	2.4					2.0~3.0		
	3.2			8.0	10.6	3.2					2.6~3.2		
TRCT	1.6			B-5 W-5	6.0	14.5	1.6	2.2	30	30	30	1.2~2.4	
	3.2				7.6	14.0	3.2					2.4~4.0	
	4.8				9.2	13.3	4.8					4.0~5.0	
	6.4				10.8	12.7	6.4					5.5~6.4	
TRDT	3.2				B-5 W-5	7.8	19.0	3.2	2.3	50	50	50	2.3~4.0
	6.4					11.0	17.5	6.4					6.0~7.0
	8.0					12.6	16.7	8.0					7.0~8.5
	9.5					14.1	15.9	9.5					9.0~9.5
12.7	17.3					14.6	12.7	12.0~12.7					
TRCS	3.2	G-6 B-6	L1~L75 (1m Increment)		9.6	13.2	4.6	2.5	50	50	50	1.0~3.2	

Minimum bending radius value is experimental ones and not guaranteed. Use them as reference.

 Ordering Example

Part Number

-

Color - Pattern

-

L

TRCT3.2

-

B-5

-

L6


Part Number		Color - Pattern	L	Unit Price/m					
Type	T			1~4m	5~9m	10~14m	15~29m	30~74m	75~99m
TRAT	0.4	B-5	L1~L100 (1m Increment)						
	0.8								
	1.6								
	2.4								
TRBT	0.8	B-5 W-5							
	1.6								
	2.4								
	3.2								
TRCT	1.6								
	3.2								
	4.8								
	6.4								
TRDT	3.2								
	6.4								
	8.0								
	9.5								
TRCS	12.7								
	3.2	G-6 B-6	L1~L75 (1m Increment)						-

Specify L dimension in 1m increment.


Corner Trims are offered for saving machining process. Trim's lip covers cut edge or uneven surface due to size difference.




Applicable Plate Thickness



TRIN (for Internal Corner)



TROUT (for External Corner)



Features

Because of the internal metal strip, it does not require adhesives to install.

Type	Material	
	Main Body	Internal Metal Strip
TRIN TROUT	Thermoplastic Elastomer (TPE)	Aluminum

Forcing trim to spread wide may split the welded part.

Part Number		Corner Direction	Color	L	A ₁	A	B ₁	B	W	Applicable Plate Thickness (T Range)	Applicable Trim	Unit Price 1 or 2 pc(s).	Volume Discount Rate 3~4	Volume Discount Rate 5~1000
Type	T													
TRIN	0.8	Internal Corner	B (Black)	50	7.6	5.6	13.5	12.3	0.8	0.6~1.2	TRAT 0.8* TRBT 0.8			
	1.6			80	8.4	6.4	12.3	12.1	1.6	1.2~2.0	TRAT 1.6* TRBT 1.6			
	2.4			100	9.2	7.2	12.2	12	2.4	2.0~3.0	TRAT 2.4* TRBT 2.4			
	3.2			100	9.6	7.6	15.2	15	3.2	2.4~4.0	TRBT 3.2* TRCT 3.2			
TROUT	0.8	External Corner		50	7.6	5.6	13.5	12.3	0.8	0.6~1.2	TRAT 0.8* TRBT 0.8			
	1.6			80	8.4	6.4	12.3	12.1	1.6	1.2~2.0	TRAT 1.6* TRBT 1.6			
	2.4			100	9.2	7.2	12.2	12	2.4	2.0~3.0	TRAT 2.4* TRBT 2.4			
	3.2			100	9.6	7.6	15.2	15	3.2	2.4~4.0	TRBT 3.2* TRCT 3.2			

While B dimension on trim side become shorter, lip part of the corner trim will cover the gap.

For orders larger than indicated quantity, please check with WOS.

 Ordering Example

Part Number

-

Color

TRIN 0.8

-

B

 Example

Can be easily attached on corners for saving machining process.

Trim's lip covers hide gaps improving finished appearances.

