



Compact Trims For Plastic Cover

■ Compact Trims for Plastic Cover with adhesive type capable of easy installation. Newly added Yellow Type is effective for alerting.



■ For Plastic Cover
CTR TT



Item	TPE	Adhesive
Specific Gravity	0.95	-
Heat Resistance	+135°C	+88°C
Low Temp. Resistance	-60°C	-15°C
Compression Set	15~25%	-

💡 TPE does not produce dioxin when burned.

Type	Material	
	Main Body	Adhesive
CTRTT CTRTT	Thermoplastic Elastomer (TPE)	Sealant

Part Number		Color	L (m)	Applicable Plate Thickness	Unit Price		
Type	T				1m	3m	5m
CTRIT	3.0	G (Gray) Y (Yellow)	L1 L3 L5	2.5~3.5			
	5.0			4.5~5.5			
CTRITR	3.0			2.5~3.5			
	5.0			4.5~5.5			




Ordering Example


Part Number	-	Color	-	L
CTRRT3.0	-	G	-	L1
CTRTR5.0	-	Y	-	L3



Example




- **Panel End Protection**
CTRTT is attached on the panel edge to prevent interference and alert a collision.




- **Filling a Gap on One Door**
CTRTR is attached to the panel edge of one door. Suitable for applications such as filling a gap with an object and insulating from splash and sound.



- **Filling a Gap between Both Doors** ①
CTR TT and CTR TR are attached to the panel edge of both doors, filling a gap between panels.






• **Filling a Gap between Both Doors** ②
CTRTR is attached to the panel edge of both doors, filling a gap between panels. (Either side can be opened first.)




Compact / Plastic Trims

■ Compact trims with no internal metal strip are easy to cut and bend as needed. With type U, corners do not protrude to the sheet metal.



■ Bending Directions



For the adhesive tape, **P.489ADTR**(EPDM), ADTS (silicon) is used.

Type		Shape	Material	Color
No Adhesive Tape	W/ Adhesive Tape			
CTRTE	CTRTEs	Rectangular	Ethylene Rubber (EPDM)	Black
CTRTS	CTRTSs		Silicon Rubber	Gray
CTRTEU	CTRTEUs	U-Shape	Ethylene Rubber (EPDM)	Black

Material Properties		
Item	EPDM	Silicon Rubber
Specific Gravity	1.2	1.2
Heat Resistance	120°C	170°C
Low Temp. Resistance	-40°C	-60°C
Compression Set	16%	27%


Compact Trims are available in 1m increment. Please note that ordering 5 pieces of L=75 means 5 rolls of 75 meter type.

Part Number		L 1mm Increment	A	B	W	t	Minimum Bending Radius mm			Applicable Plate Thickness	Unit Price (1m)		
Type	T						Bending Directions ①	Bending Directions ②	Bending Directions ③		No Adhesive Tape	W/ Adhesive Tape	
Ethylene Rubber (EPDM) Rectangular	1.6	L1~L75 (1m Increment) * W/ Adhesive Tape * L1~L2	5.2	10	1.4	1.9	R70	R50	R30	1.0~1.6			
CTRIE	2.3		6	10	2.2	1.9			R40	2.0~2.3			
CTRTES (W/ Adhesive Tape)	3.2		6.9	10	3.1	1.9			R30	3.0~3.2			
Silicon Rubber Rectangular	1.6		5.2	10	1.4	1.9			R40	1.0~1.6			
CTRTS	2.3		6	10	2.2	1.9			R30	2.0~2.3			
CTRTSS (W/ Adhesive Tape)	3.2		6.9	10	3.1	1.9			R40	3.0~3.2			
Ethylene Rubber (EPDM) U-Shape	0.8			4	6	1	1.4	R30	R30	R30	0.6~1.2		
CTRTU	1.6			4.4	7	1.4	1.4			R30	1.0~1.6		
CTRTUS (W/ Adhesive Tape)	2.3			5.3	8	2.1	1.5			R30	2.0~2.3		




Ordering Example **Part Number** - **L**
CTRTE1.6 - **L32**

■ Translucent plastic trims blend well with painted sheet metal and stainless steel surfaces.



■ Bending Directions



Part Number		L 1mm Increments	A	W	Minimum Bending Radius mm			Applicable Plate Thickness
Type	No.				Bending Directions ①	Bending Directions ②	Bending Directions ③	
PTRTN	1	10~2000	3.3	1.3	R150	R300	R200	1.0~1.1
	2		3.7	1.7				1.2~1.5
	3		4.4	2.4				1.6~2.2
	4		5.3	3.3				2.3~3.2



Ordering Example: **Part Number** - **L**
PTRTN1 - **200**

[illegible]