

Joints for Factory Frames

RoHS10

Part Number	Material
FFB1, FFB2	EN AC-46100 Equiv.
FFB3-FFB5	EN AC-46100 Equiv.

Reference Tightening Torque: 6.8N/m

The shape of FFB3 ~ FFB5 may be partially altered for product improvements.

FFB1

FFB2

FFB3

FFB4

FFB5

Part Number	Type	No.	Mass (g)	Included Screw and Nut		Unit Price
				Size	Quantity	
FFB		1	88	M5-18	2	
		2	168			
		3	172			
		4	92	M5-15	4	
		5	145	M5-20	2	
				M5-25	1	
				M5 Nut		

RoHS10

Part Number	Material
FFB6-FFB10	EN AC-46100 Equiv.

Reference Tightening Torque: 6.8N/m

The shape may be partially altered for product improvements.

FFB6

FFB7

FFB8

FFB9

FFB10

Part Number	Type	No.	Mass (g)	Included Screw and Nut		Unit Price
				Size	Quantity	
FFB		6	35	M5-12	1	
		7	80		2	
		8	84		1	
		9	110	M5-20		
		10	145		2	

Alteration	Code	Spec.
Set Screw	SET	Include 4 set screws (M4-6) with FFB9 as a set. Applicable to FFB9 only.

RoHS10

Part Number	Material
FFB11-FFB15	EN AC-46100 Equiv.

Reference Tightening Torque: 6.8N/m

FFB11

FFB12

FFB13

FFB14

FFB15

Part Number	Type	No.	Mass (g)	Included Screw and Nut		Unit Price
				Size	Quantity	
FFB		11	250	M5-18	1	
		12	88	M5-20	1	
		13	88	M5 Nut	1	
		14	35	M5-20	2	
		15	140	M5 Set Screw	1	
				M5-18	3	
				M8-35	1	



Ordering Example

Part Number
FFB1



Example

