


Extruded Brackets - For 1 Slot


For 8-45 Series (Slot Width 10mm) Aluminum Extrusions



■ **Features:** Extruded Brackets with two mounting holes on one side can connect extrusions more securely.

■ **Thick Brackets**

HBLTSW8



RoHS10


M Material: EN AC-51400-T5 Equiv.
S Surface Treatment: Anodize

Part Number	Mass (g)	Applicable Screw, T Nut			Allowable Load (N)	Unit Price (1-99 pc(s))	Volume Discount Rate (100-200)
		Screw	Quantity	T Nut			
HBLTSW8	113	CBM8-20	4	HNTT8-8	4	3087	

■ **Features:** Extruded Brackets with two mounting holes on one side can connect extrusions more securely.

■ **Triangle Brackets**

HBLDSWT8-45



RoHS10



M Material: A6N01SS-T
S Surface Treatment: Anodize

Part Number	Mass (g)	Applicable Screw, T Nut			Allowable Load (N)	Unit Price (1-99 pc(s))	Volume Discount Rate (100-200)
		Screw	Quantity	T Nut			
HBLDSWT8-45	235	CBM8-15	4	HNTT8-8	4	3087	

■ **Features:** Brackets to connect 45, 30 square Extrusions.

■ **Assembly Brackets for Different Extrusion Sizes**


HBLTS845-6L
HBLTS845-6R



M Material: EN AC-51400-T5 Equiv.
S Surface Treatment: Anodize

Part Number	Mass	Applicable Screw, T Nut			Allowable Load	Unit Price	Volume Discount Rate	
	(g)	Screw	Quantity	T Nut	(N)	1-99 pc(s)	100-200	
HBLTS845-6L	78	CBM6-20	1	HNTT8-6	1	-		
HBLTS845-6R		CBM6-15		HNTT6-6				
		CBM6-20		HNTT8-6				
		CBM6-15		HNTT6-6				


ex Example



■ **Features:** Extruded Brackets to connect 50 square Extrusions.

For 50 Sq.

HBLTS8-50




M Material: EN AC-51400-T5 Equiv. **S** Surface Treatment: Anodize

Part Number	Mass (g)	Applicable Screw, T Nut			Allowable Load (N)	Unit Price (1-99 pc(s))	Volume Discount Rate (100-200)
		Screw	Quantity	T Nut			
HBLTS8-50	89	CBM8-20	2	HNTT8-8	2	2058	

■ **Features:** Extruded Brackets for 50 square Extrusions with two mounting holes on one side.

For 50 Sq.

NBLUW8-50
HBLUW8-50



Both sides and screw holes of NBLUW8-50 is not anodized.


Type	M	Material	S	Surface Treatment
NBLUW8-50		EN AW-6063-T5 Equiv.		Anodize
HBLUW8-50		EN AC-51400-T5 Equiv.		Anodize

Part Number	Mass (g)	Extrusion Series	Applicable Screw, T Nut			Allowable Load (N)	Unit Price 1-99 pcs	Volume Discount Rate 100-200
			Screw	Quantity	T Nut			
NBLUW8-50	223	HFS8-5050	CBM8-15	2	HNTT8-8	4	2793	
			CBM8-25					
HBLUW8-50		HFS8-5050	CBM8-15					
			CBM8-25					

■ **Features:** Extruded Brackets to connect 60 square Extrusions.

For 60 Square

NBLUW8-60
HBLUW8-60



Both sides and screw holes of NBLUW8-60 is not anodized.

Type	M	Material	S	Surface Treatment
NBLUW8-60		EN AW-6063-T5 Equiv.		Anodize
HBLUW8-60		EN AC-51400-T5 Equiv.		Anodize

Part Number	Mass (g)	Extrusion Series	Applicable Screw, T Nut			Allowable Load (N)	Unit Price (1-99 pcs)	Volume Discount Rate 100-200
			Screw	Quantity	T Nut			
NBLUW8-60	275	HFS8-6060	CBM8-15	2	HNTT8-8	4	2793	
HBLUW8-60			CBM8-25					
			CBM8-15					
			CBM8-25					

Ordering Example
Part Number
HBLTS845-6L
HBLUW8-50

Alterations (C, SET, SST, SEU, SSU, SEP, SSP, SEC)
SET

Alterations	Code	Spec.	Applicable Bracket
Mounting Hole Alteration for Cover	C	Adds taps on a bracket for cover mounting. (M5 on Both Sides) (Mounting Screw HCBM on P.754) *Tapping Direction: For HBLTS845-6□, tapping is only applied on the narrow side of the offset.	HBLTSW8
			HBLTS845-6L*
			HBLTS845-6R*
			HBLTS8-50
			HBLUW8-50
			HBLUW8-60

Alterations	Code	Spec.	Applicable Bracket
Applicable Screws and Nuts Set	SET	Applicable screws and nuts for fixing the brackets on extrusions come in a set. (Adds to the bracket price) (Ex.) When HBLTSW8 is specified:	HBLTSW8
	SST		HBLTS845-6L
	SEU		HBLTS845-6R
	SSU		HBLTS8-50
	SEP		NBLUW8-50
	SSP		HBLUW8-50
	SEC		NBLUW8-60
	SEP		HBLUW8-60
	SST		NBLUW8-60
	SSU		NBLUW8-60
	SSP		NBLUW8-60
	SEC		NBLUW8-60

*Included Screw is not RoHS compliant when -SET, -SEU or -SEP are specified.