


Caster Dual Wheel Type

Medium Load / Ultra Heavy Load

Medium Load

CWM-P

Main Body	Wheel	Bearing
M Material S Surface Treatment	M Material (Color)	M Material (Color)
EN 1.0320 Equiv. (hot coiled)	Trivalent Chromate	Nylon (Black)
		Incorporated
		None



RoHS 10

Main Body	Part Number		Wheel Material	H	d	r	Allowable Load (N)	Mass (g)	Unit Price
	Type	D							
Swivel	CWM-P	38	N (Nylon)	64	8.8	44	1200	450	
		50		77		49	1500	470	





Ordering Example
Part Number - Wheel Material
CWM-P38 - N

Features: Has the max. allowable load in our lineup. Can be used for traction of large processing machines and dedicated devices by motor power.

Ultra Heavy Load

CKXJ




RoHS 10

Main Body	Wheel	Bearing
M Material S Surface Treatment	M Material (Color)	M Material (Color)
EN 1.0320 Equiv. (hot coiled)	Trivalent Chromate	MC Nylon (Blue)
		Incorporated
		Incorporated

Main Body	Part Number		Wheel Material	H	r	Allowable Load (N)	Mass (g)	Unit Price	
	Type	D						1 ~ 4 pc(s).	5 ~ 10 pcs.
Swivel	CKXJ	100	M (MC Nylon)	150	97	10000	5300		
		125		170	109	13000	5700		
		150		200	121	15000	6300		



Ordering Example
Part Number - Wheel Material
CKXJ100 - M




Caster Dual Wheel Type

Heavy Load Steel / Stainless Steel

Heavy Load - Steel -

CWMJ

Main Body	Wheel	Bearing
M Material S Surface Treatment	M Material (Color)	M Material (Color)
EN 1.0320 Equiv. (hot coiled)	Trivalent Chromate	MC Nylon (Blue)
		Incorporated
		Incorporated




RoHS 10

Main Body	Part Number		Wheel Material	H	D1	B	A	F	d	t	E	r	Allowable Load (N)	Mass (g)	Unit Price
	Type	No.													
Swivel	CWMJ	50	N (MC Nylon)	75	42	38	84	64	8.5	3.2	12	49	4000	812	
		65		93	57	48	100	78	10.5	4.5	14	57	5000	1530	
		75		102	65								6000	1620	

Heavy Load - Stainless Steel -

CWG

Main Body	Wheel	Seal	Bearing
M Material S Surface Treatment	M Material (Color)	M Material (Color)	M Material (Color)
EN 1.4301 Equiv.	Monomer Casting Nylon (Blue)	Electrically Conductive MC Nylon (Black)	Polycetal
			Incorporated
			Incorporated



RoHS 10

Main Body	Part Number		Wheel Material	H	A	F	d	E	r	Allowable Load (N)	Mass (g)	Unit Price	
	Type	D										Monomer Casting Nylon	Electrically Conductive MC Nylon
Swivel	CWG	50	N (Monomer Casting Nylon) D (Electrically Conductive MC Nylon)	75	84	64	8.5	12	43	4000	760		
		65		93									
		75		102	100	78	10.5	15	54	5000	1060		



Ordering Example
Part Number - Wheel Material
CWMJ50 - N
CWG50 - D