


Leveling Mount

Standard



Part Number		L	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	M-A				NFJN	NFJNS
NFJN (Stainless Steel) NFJNS	5 - 30	40.5	1.5	15		
	5 - 60	70.5		19		
	6 - 40	51		21		
	6 - 80	91	2.1	28		
	8 - 50	68.1		50		
	8 - 100	118.1		65		
	10 - 75	94.6	4.3	88		
	10 - 100	119.6		100		
	12 - 50	78		142		-
	12 - 75	103	4.9	166		
	12 - 100	128		184		
	12 - 125	153		200		
	12 - 150	178	5.9	219		
	16 - 75	107		287		
	16 - 100	132		317		
	16 - 130	162	8.8	356		
	16 - 150	182		383		
	16 - 180	212		422		
	20 - 100	135		493		
	20 - 130	165		557		
	20 - 150	185		605		
	20 - 180	215		671		




For NFJN only. No plating on alteration-applied sections. For alterations for 31 or more pieces, please request a quotation.

Alterations	Square Flats	Hex Flats	Wrench Flats	Hex Wrench Socket Machining
Code	WC	WK	SC	WN
Spec.	Ordering Code WC Applicable when 20≥M≥10	Ordering Code WK Applicable when 20≥M≥10	Ordering Code SC Applicable when 20≥M≥10	Ordering Code WN Applicable when 20≥M≥10
	M WC ℓ 10 6 10 12 8 10 16 10 12 20 12 13.5	M WK ℓ 10 6 10 12 8 10 16 10 12 20 13 10	M W ℓ1 SC 10 8 8 20 12 10 10 20 16 13 10 20 20 17 10 20	M WN ℓ 10 4 5 12 5 6 16 8 8 20 8 8

Leveling Mount

Non-Slip



Part Number		L	Allowable Vertical Load (kN)	Mass (g)	Unit Price							
Type	M-A				FJGN	FJGM				FJGNS	FJGMS	
FJGN FJGM FJGNS (Stainless Steel) FJGMS (Stainless Steel)	8- 50 8-100 10- 75 10-100 12- 75 12-100* 12-125* 12-150 16- 75 16-100* 16-130* 16-150 16-180* 20-100* 20-130* 20-150 20-180*	Rubber Material	70.5 120.5 97 122 106 131 156 181 110 135 165 185 215 138 168 188 218	3.9 3.9 4.3 4.3 4.9 4.9 4.9 4.9 5.9 5.9 5.9 5.9 6.8 6.8 6.8 6.8 6.8	50 70 91 103 178 196 212 231 301 331 370 397 436 148 173 194 220	-	-	-	-	-	-	-

You cannot select the rubber material for FJGN and FJGNS. (Elastomer is used.) * PVC rubber applicable sizes

