


Slide Locks / Hooks

Grip Handles for Aluminum Extrusions / Reinforcement Covers



RoHS10

HSUKJ



Material: EN 1.4301 Equiv.
Surface Treatment: Buffed Finish

Part Number	Type	No.	L	Screw, Nut			Unit Price	Volume Discount Rate
				Screw	Quantity	Post-Assembly Fitting Nut		
HSUKJ	5	61		SHFBS4-6		HNTASN5-4		
	6	71		SHFBS4-8	4	HNTASN6-4	4	
	8	81		SHFBS4-10		HNTASN8-4		

This product is for mounting to aluminum extrusions only.




Ordering Example

Part Number

HSUKJ5



Example




Keep gap A larger than 4mm.
(In the app. example, the gap is 4.5mm.)

Alterations	Code	Spec.	Type	No.
Set of applicable Screws and Nuts	SET	Applicable Screw	HSUKJ	5
				6
				8




RoHS10

HKKJ



Material: EN 1.4301 Equiv.
Surface Treatment: Buffed Finish

HKKT



Material: EN 1.4301 Equiv.
Surface Treatment: Buffed Finish


Part Number	Allowable Load (N)	Mass (g)	Unit Price	Volume Discount Rate
Type			1 ~ 9 pc(s).	10~50
HKKJ	196	36		
HKKT	196	45		



Example




Recommended Screws and Nuts when Mounting on the Aluminum Extrusions				
Applicable Extrusion	Screw	Quantity	Post-Assembly Fitting Nut	Quantity
HFS5	SHFBS5-8		SHNTP5-5	
HFS6	SHFBS5-10	2	SHNTP6-5	
HFS8(8-45)	SHFBS5-15		SHNTP8-5	2



RoHS10

Handle


HFHDL5-35
HFHDLB5-35 (Black Anodize)



Applicable nut is HNTT5.

Handle Cover

HFC5-35L
HFC5-35R




Material: EN AC-51400-T5 Equiv.
Surface Treatment: Anodize
Material: Polyamide (Black, Light Gray)

Part Number	L 1mm Increment	Mass kg/m	Sectional Area mm ²	Unit Price Less than 300mm 1 ~ 50 pc(s).	Unit Price/m 300mm or more 1 ~ 50 pc(s).
HFHDL5-35 HFHDLB5-35 (Black Anodize)	50~2000	0.73	271		

Part Number	Color	Mass (g)	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10~19	20~50
HFC5-35L	B (Black)	1.9			
HFC5-35R	S (Light Gray)				


Light gray is the default color unless specified.



RoHS10

Reinforcement Covers

HFPCV3
HFPCV5



Material: EN AW-6063-T5 Equiv.
Surface Treatment: Anodize

Part Number	Type	No.	L 1mm Increment	Mass kg/m	Sectional Area mm ²	300mm or Less		300mm or More	
						Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10~19	Unit Price/m 1 ~ 9 pc(s).	Volume Discount Rate/m 10~19
HFPCV		3	50~3000	0.12	45.4				
		5		0.13	47.4				



Ordering Example

Part Number - L, Color

HFHDL5-35 - 400

HFC5-35L - S


HFPCV3 - 800



Example

Plastic Plate Reinforcement

Handle Mounting






Alterations

Part Number - L - (Alteration Code)

HFPCV5 - 300 - LCT45

Alterations	45° Cut	
Code	LCT45	RCT45
Spec.	One End 45° Miter Cut Ex. LCT45 	
HFPCV	3	450
	5	450