

Offset Pull Handles


Outside Mount




Round Bar Pull Handles



Type	Material	Surface Treatment
UHFSN	EN 1.0038 Equiv.	Chrome Plating
UHFSNB	EN 1.0038 Equiv.	Black Oxide
UHFNSS	EN 1.4301 Equiv.	Buffing



Example




Part Number	L	L1	L2	Unit Price
Type				
UHFSN (Steel)	110	130	80	
UHFSNB (Steel)	120	140	90	
UHFNSS (Stainless Steel)	125	145	95	
	160	180	130	
	200	220	170	
	250	270	220	

With Mounting Tabs



The pedestals are rotatable in any desired position.



Type	Material	Surface Treatment	Accessory
UHFNGG	EN 1.0715 Equiv.	Chrome Plating	Pedestal G
UHFNSG	EN 1.4301 Equiv.	Buffing	Pedestal S
UHFNEAG	Aluminum Alloy	Clear Anodize	Thread



Handles are shipped with the pedestals uninstalled.

Part Number	L	Pedestal Selection	L1	Allowable Load (N)	Reference Mass (g)	Unit Price
Type						
UHFNGG (Steel)	48	G (Zinc Die Cast) S (EN 1.4301 Equiv.)	86	2000	90	
UHFNSG (Stainless Steel)	66		104		100	
UHFNEAG (Aluminum)	88		126		114	
	100		138		122	
	110		148		127	
	120		158		134	
	125		163		136	
	160		198		158	

With Mounting Tabs



Part Name	Material	Surface Treatment	Accessory
Handles	EN AW-6063 Equiv.	Clear Anodize	SHFBSS-12
Plate	EN AW-6063 Equiv.	Clear Anodize	EN 1.4301 Equiv.

Part Number	L	L1	R	R1	Reference Mass (g)	Unit Price
Type						
UHFNG	100	110	100	145	50	
	120	130	120	165	52.5	
	125	135	125	170	54	



Example




The default L dimension is 100 unless specified.

Ordering Example: Part Number - Pedestal Selection
UHFSN160
UHFNGG100 - G
UHFNG120

Aluminum Type



HHDNFA



Material: Aluminum Alloy
Surface Treatment: Baked Paint



Example




Part Number	Allowable Load (N)	Mass (g)	Unit Price
Type			
HHDNFA	1100	105	

Cast Offset



UWASNDF



Material: EN 1.4301 Equiv.
Surface Treatment: Buffing


Part Number	L	L1	Allowable Load (N)	Mass (g)	Unit Price
Type					
UWASNDF	80	98	500	100	
	100	118		110	
	150	168		130	

Ordering Example: Part Number
HHDNFA112
UWASNDF100

Aluminum Tube Pull Handles



UHFAP
UHFAPFC (L Configurable)




Part Name	Material
Tube Handle	EN AW-6063 Equiv.
Elbow	Glass Fiber Reinforced Nylon

Small Diameter Aluminum Tube



UHFAPC
UHFAPFC (L Configurable)



Part Name	Material
Tube Handle	EN AW-6063 Equiv.
Elbow	Polycarbonate

L Fixed

Part Number	L	Applicable Screw	Unit Price
Type			
UHFAP (L Fixed)	150	Flat Head Screw M8	
	200		
	250		
	300		
	400		
	500		

L Configurable

Part Number	L	Applicable Screw	Unit Price
Type			
UHFAPFC (L Configurable)	100-150	Flat Head Screw M8	
	151-200		
	201-250		
	251-300		
	301-400		
	401-500		

L Fixed

Part Number	L	Applicable Screw	Unit Price
Type			
UHFAPC (L Fixed)	100	Hex Socket Head Cap Screw M6	
	150		
	200		
	250		
	300		

L Configurable

Part Number	L	Applicable Screw	Unit Price
Type			
UHFAPFC (L Configurable)	100-150	Hex Socket Head Cap Screw M6	
	151-200		
	201-250		
	251-300		

Ordering Example: Part Number - L
UHFAP 150
UHFAPFC - 225
"- " is not necessary for L Fixed Type.