



Manifold Blocks - Hydraulic / Pneumatic

Lateral Through Hole, L-Shaped Hole



Manifold Blocks - Pneumatic

Lateral and Vertical Through Hole / Lateral Through Hole, Upper Hole



For details of recommended tapered male thread tightening torque and through pilot hole, see P.1224.

Manifold Blocks - Hydraulic

BMUN

(Max. Operating Pressure: 20.6MPa≈210kgf/cm² or less) Thread: JIS B0203 Rc(PT) Material: EN 1.0038 Equiv. Surface Treatment: Trivalent Chromate

Manifold Blocks - Pneumatic

BMUAN

(Max. Operating Pressure: 1MPa≈10kgf/cm² or less) Thread: JIS B0203 Rc(PT) Material: Aluminum Alloy

Part Number		No.	d1 Rc(PT)	d2 Rc(PT)	Unit Price
Type					
BMUN	1	33	3/8	3/8	
		13	1/8	3/8	
	2	22	1/4	1/4	
		23	1/4	3/8	
		34	3/8	1/2	
		22	1/4	1/4	
	3	23	1/4	3/8	
		33	3/8	3/8	
		12	1/8	1/4	
	4	22	1/4	1/4	
		23	1/4	3/8	
		23	1/4	3/8	
	5	23	1/4	3/8	
	6	34	3/8	1/2	

Part Number		No.	d1 Rc(PT)	d2 Rc(PT)	Unit Price
Type					
BMUAN	1	22	1/4	1/4	
		11	1/8	1/4	
	2	12	1/8	1/4	
		22	1/4	1/4	
		11	1/8	1/8	
		12	1/8	1/4	
	3	22	1/4	1/4	
		12	1/8	1/4	
		22	1/4	1/4	
	4	12	1/8	1/4	
		22	1/4	1/4	
		12	1/8	1/4	
	5	12	1/8	1/4	
	6	22	1/4	1/4	

Ordering Example
Part Number
BMUN2-22
BMUAN4-22

For details of recommended tapered male thread tightening torque and through pilot hole, see P.1224.

Manifold Blocks - Pneumatic

BMIAN

(Max. Operating Pressure: 1MPa≈10kgf/cm² or less) Thread: JIS B0203 Rc(PT) Material: Aluminum Alloy

Manifold Blocks - Pneumatic

BMSLN

(Max. Operating Pressure: 1MPa≈10kgf/cm² or less) Thread: JIS B0203 Rc(PT) Material: Aluminum Alloy

Part Number		No.	d1 Rc(PT)	d2 Rc(PT)	Unit Price
Type					
BMIAN	1	11	1/8	1/8	
		22	1/4	1/4	
	2	11	1/8	1/8	
		12	1/8	1/4	
		22	1/4	1/4	
		11	1/8	1/8	
	3	22	1/4	1/4	
		11	1/8	1/8	
		22	1/4	1/4	
	4	11	1/8	1/8	
		12	1/8	1/4	
		22	1/4	1/4	
	5	12	1/8	1/4	
	6	11	1/8	1/8	

Part Number		No.	d1 Rc(PT)	d2 Rc(PT)	Unit Price
Type					
BMSLN	2	24	1/4	1/2	
		33	3/8	3/8	
	3	44	1/2	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
		23	1/4	3/8	
	4	24	1/4	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
	5	24	1/4	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
	6	23	1/4	3/8	

Ordering Example
Part Number
BMIAN3-22