



Hydraulic Fittings


Straight




Part Number		T1	T2	L	l1	l2	B	Unit Price	
Type	No.	R (PT)	R (PT)					YCPPT	YCPST
YCPPT YCPST	11	1/8	1/8	26	10	12	12		
	12	1/8	1/4	31	10	13	17		
	13	1/8	3/8	33	10	15	21		
	22	1/4	1/4	34	13	13	17		
	23	1/4	3/8	36	13	15	21		
	33	3/8	3/8	37	15	15	21		
	34	3/8	1/2	40 (46)	14 (16)	17 (19)	26 (22)		
	44	1/2	1/2	43	17	17	26 (22)		
	46	1/2	3/4	46 (48)	17 (18)	19	32 (27)		
	66	3/4	3/4	48	19	19	32 (27)		



Part Number		T	F	L	l1	l2	B	Unit Price	
Type	No.	R (PT)	G (PF)					YCPFP	YCPFS
YCPFP YCPFS	11F	1/8	1/8	31	10	13	14		
	12F	1/8	1/4	34	10	16	19		
	13F	1/8	3/8	37	10	17.5	22		
	21F	1/4	1/8	34	13	13	14		
	22F	1/4	1/4	37	13	16	19		
	23F	1/4	3/8	38.5	13	17.5	22		
	31F	3/8	1/8	37	15	13	19		
	32F	3/8	1/4	38.5	15	16	19		
	33F	3/8	3/8	40.5	15	17.5	22		
	34F	3/8	1/2	45	15	20	27		




Part Number		T	F	L	l1	l2	B	Unit Price	
Type	No.	R (PT)	G (PF)					YCPFG	
YCPFG	22F	1/4	1/4	38	13	8	19		
	33F	3/8	3/8	42	15	8	22		
	44F	1/2	1/2	50	18	10	27		




Part Number		T	F	L	l1	B	Unit Price	
Type	No.	Rc (PT)	G (PF)				YCPFFP	YCPFFSP
YCPFFP YCPFFSP	22F	1/4	1/4	33	16	19		
	33F	3/8	3/8	37	18	22		
	44F	1/2	1/2	42	20	27		

Specifications Applicable Fluids : Oil, Water
Max. Operating Pressure : 20.6MPa (210kgf/cm² or less)



Part Number		T	F	L	l1	l2	B	Unit Price	
Type	No.	R (PT)	G (PF)					YCPF	YCPFS
YCPF YCPFS	11F	1/8	1/8	27	10	11	14		
	12F	1/8	1/4	32	10	13	19		
	13F	1/8	3/8	34	10	15	22		
	21F	1/4	1/8	32	13	11	14		
	22F	1/4	1/4	34	13	13	19		
	23F	1/4	3/8	36	13	15	22		
	31F	3/8	1/8	34	15	11	19		
	32F	3/8	1/4	36	15	13	19		
	33F	3/8	3/8	38	15	15	22		
	34F	3/8	1/2	42	15	17	27		



Part Number		T	F	L	ℓ ₁	ℓ ₂	B	Unit Price	
Type	No.	R (PT)	G (PF)					YCPFG	YCPFGS
YCPFG YCPFGS	11F	1/8	1/8	31	10	6	14		
	12F	1/8	1/4	34	10	8	19		-
	21F	1/4	1/8	34	13	6	14		-
	22F	1/4	1/4	38	13	8	19		
	23F	1/4	3/8	39	13	8	22		-
	32F	3/8	1/4	39	15	8	19		-
	33F	3/8	3/8	42	15	8	22		