


Flat Tension Levers / Flat Tension Levers with Hex Socket

Tension Levers / Disengaging Tension Levers / Stationary Levers

Flat Tension Levers



RoHS10




Part Number		L Selection				Lf	R	H	H1	h	A	B	D	d	Number of Serrated Teeth	Fmax. Max. Load (N)	Pmax. Max. Tightening Force (kN)	Reference Mass (g)		Unit Price	
Type	M	(Threaded Type only)																LFTM	LFTMF	LFTM	LFTMF
Threaded LFTM Tapped LFTMF	8	30	40	50		18	100	12	16	19	10	25	33	13	22	120	10	185	160		
	10	30	40	50	60	21	130	13.5	17.5	22	12	30	41	19	26	180	16	340	300		
	12	30	40	50	60											300	23	350	300		
	16		40	50	60	27	150	17	22	28	14	35	45	23	36	660	43	580	450		

Part Number		L Selection				R	H	H ₁	h	S	A	B	D	d	Number of Serrated Teeth	Fmax. Max. Load (N)	Pmax. Max. Tightening Force (kN)	Reference Mass (g)	Unit Price
Type	M																		
Offset LFTMA	8	32	40	50		100	12.5	16.5	20.5	1.5	8	20	32	13.5	22	120	10	155	
	10	32	40	50	63	120	15	19	24.5		10	25	36	16		180	16	250	
	12	40	50	63		130	16	20.5	26.5	2	12	30	40	19	26	300	23	350	
	16	40	50	63		145	20	25	31.5			32	45	23	36	660	43	520	

Flat Tension Levers with Hex Socket



RoHS10




Part Number		L Selection (Threaded Type only)		R		Lf	H	H ₁	h	A	B	b	D	d	Number of Serrated Teeth	Fmax. Max. Load (N)	Pmax. Max. Tightening Force (kN)	Reference Mass (g)		Unit Price				
Type	M																	Stationary	10mm Increment (LFTMR only)	Steel	Stainless Steel	LFTMR	LFTMRF	LFTFRS
Threaded LFTMR LFTMRF LFTFRS	8	30	40	50	100	80~120	8	12	16	19	10	25	3	33	13	22	120	10	185	250				
	10	30	40	50	60	130	100~150	11	13.5	17.5	22	12	30	5	41	19	26	180	16	340	400			
	12	30	40	50	60													300	23	350	400			
	16	40	50	60	150	120~180	14	17	22	28	14	35						660	43	580	680			

Ordering Example: Part Number - L - R
LFTM 8 - 30 - 110
LFTMF 8 - 30 - 110
LFTMRF 8 - 30 - 110
LFTFRS 8




Tension Levers



Part Number		L			S	S ₁	d	Number of Serrated Teeth	F _{Max.} Load N	P _{Max.} Tightening Force kN	Reference Mass (g)	Unit Price	
Type	M	Selection										T _{LDM}	T _{ALDM}
T _{LDM} A _{LDM}	10	30	40	50	4	9	16	22	300	12	210		
	12	30	40	50					60	420	18	215	
	16	40	50	60	3	3	22		670	33	220		

Ordering Example: Part Number - L
TLDM10 - 30


Disengaging Tension Levers



Stationary Levers



RoHS10



Part Number		L	Handle Color	L3	d	LRGN, LRGB, LRGNS			LBG, LBGB, LBGS			Reference Mass (g)	Unit Price									
Type	M (Coarse)					D1	H1	L1	D2	H2	L2		LRGN	LRGB	LRGNS	LBG	LBGB	LBGS				
Handle Type LRGN LRGB LRGNS	6	63	R (Red)	12	8	17	40	23	20	18	45	25										
		80											40	62	32							
		100											60	82	40							
	8	80		20	10	21	50	30	25	23	57	53										
100		50											77	65								
125		75											102	81								
Ball Knobs LBG LBGB LBGS	10	100		B (Black)	25	12	25	65	35	30	28	72	97									
		125												60	97	119						
		160												95	132	149						
	12	125			30	14	28	86	39	35	32	93	163									
160		74	128											205								
200		114	168											253								

The handle color for LRGB and LBGB is black only.

Ordering Example: Part Number - L - R - Handle Color
LBGS6 - 63 - R - B
LBGS8 - 100 - B