



Arched Pull Handles / Phenol Pull Handles



Arched Pull Handles

UWSY

■Features: Designed to be aesthetically pleasing and easy to grip.



Material: EN 1.4301 Equiv.
Surface Treatment: Buffing


Part Number Type	L	L1	H	h	Allowable Load (N)	Mass (g)	Unit Price
UWSY	100	138	42	27	500	351	
	150	190	44	29		448	

Ordering Example
Part Number
UWSY100



Phenol Pull Handles

UPCFN




Material
Handle Phenol Resin
Thread Brass (Insert)

Part Number Type	L	L1	M	H	Mass (g)	Allowable Load (N)	Unit Price
UPCFN	90	110	6	50	90	1100	
	114	132			105	1100	
	120	142			140	700	
	140	162	8	60	155	600	
	160	182			170	600	
	180	202			200	500	
	200	222			210	470	


Ordering Example
Part Number
UPCFN114

Pull Handles - Non-Metal / T-Shaped



Nylon Type

UPFN



Material
Handle Glass Fiber Reinforced Nylon 6
Thread Brass (Insert)


Part Number Type	L	Handle Color	L1	H	h	M (Coarse)	Allowable Load (N)	Mass (g)	Unit Price
UPFN	26	B (Black)	121	37	29	6	500	55	B (Black)
		W (White)	133	40	32	8		60	W (White), M (Orange), R (Red)
		M (Orange)						62	

The default handle color is black unless specified.

Ordering Example
Part Number
UPFN26 - L - 105 - B

For Panels

HHDS
HHDSW
HHDSA
HHDS



Type
HHDS Polycarbonate (Black)
HHDSW Polycarbonate (White)
HHDSA EN AC-46100 Equiv.
HHDS EN 1.4301 Equiv.

Material
Polycarbonate (Black)
Polycarbonate (White)
EN AC-46100 Equiv.
EN 1.4301 Equiv.


Surface Treatment
-
-
Baked Paint: Silver Metallic
Buffing

Part Number Type	L	L1	H	h	A	Mass (g)	Unit Price
HHDS, HHDSW, HHDSA, HHDS	90	110	32	24	13	17	HHDS
	104	127	37	27.7	16	25	HHDSW
	122	149	43.3	32.5	19	42	HHDSA
						102	HHDS

There is no allowable load for the panel mounting handles.

Rubber Type

UGFN




Material
Handle EPDM Rubber (Mat Black)
Thread Brass (Insert)

Part Number Type	L	L1	Mass (g)	Unit Price
UGFN (Rubber Type)	40	50	10	
	53	63	12	
	70	80	15	

The allowable load value not provided since unfeasible to measure.

T-Shaped

TSPF



Material
Handle Glass Fiber Reinforced Nylon (Mat Black)
Thread EN 1.0038 Equiv. (Insert)

Surface Treatment
-
Trivalent Chromate

Part Number Type	D	M	Lf	d	Mass (g)	Unit Price
TSPF	50	3	20	11	26	
		4			28	
		5			30	
		5			46	
	80	6	25	16	50	
		6			50	
		8			56	
		8			56	

Ordering Example
Part Number
HHDS90
UGFN70
TSPF50 - M - 4