

Arched Pull Handles / Cast Pull Handles

Outside Mount




Arched Pull Handles

UWSD



RoHS10



Features: Designed to be aesthetically pleasing and easy to grip.

Part Number Type	L	L1	H	h	H1	Allowable Load (N)	Mass (g)	Unit Price
UWSD	100	139	42	27	21	500	337	
	150	190	44	29	17		434	



Back Side




Ordering Example Part Number UWSD150

Cast Pull Handles

UWASND



RoHS10




Part Number Type	L	L1	H	h	T	A	W	R	N Through	Countersink	Allowable Load (N)	Mass (g)	Unit Price
UWASND	80	96	32	20	6	18	12	20	4.5	8.5	500	97	
	100	116						23				116	
	150	170	46	30	9	22	16	30	6.5	12.5		301	
	200	220	46	30	9	22	16	30	6.5	12.5		354	

Cast Pull Handles

UWANDC



RoHS10



Part Number Type	L	L1	H	h	t	R	d	N	Allowable Load (N)	Mass (g)	Unit Price
UWANDC	105	120	30	24	5	25	7.5	5.5	500	83	
	115	130	33	27	5	26	7.5	5.5		90	
	125	145	34	28	5.5	30	10	6.5		106	

Ordering Example Part Number UWASND100 UWANDC125

Folding Pull Handles / Pull Handles with Caps / Aluminum Tube Pull Handles

Outside Mount




Folding Pull Handles

Type	Material	Surface Treatment
UWFASN	EN 1.1191 Equiv.	Chrome Plating
UWFASNS	EN 1.4301 Equiv.	Buffing



RoHS10




Part Number Type	L	L1	Allowable Load (N)	Mass (g)	Unit Price	
					UWFASN	UWFASNS
UWFASN (Steel)	138	100	650	150		
	158	120	550	160		
	180	142	520	180		
	218	180	500	200		


Ordering Example Part Number UWFASN138

Pull Handles with Caps

Type	Handles		Cap	
	Material	Surface Treatment	Material	Color
HHDG	EN AC-46100 Equiv.	Baked Paint	ABS	White
HHDGS	EN 1.4301 Equiv.	Buffing	ABS	White



RoHS10



Part Number Type	L	Mass (g)	Applicable Screw	Qty.	Unit Price	
					HHDG	HHDGS
HHDG	100	62	Flat Head Screw M5	2		
HHDGS						


Ordering Example Part Number HHDG100

Nut for Pull Handles with Caps

HHPUW



RoHS10



Part Number Type	P	Applicable Handle	Unit Price	Volume Discount Rate
			1 ~ 9 pc (s).	10 ~ 100
HHPUW	100	HHDG100 HHDGS100		


Ordering Example Part Number HHPUW100

Aluminum Tube Pull Handles

UWAPN UWAPF (L Configurable)



RoHS10




Part Name	Material
Tube Handle	EN AW-6063 Equiv.
Elbow	Glass Fiber Reinforced Nylon

Small Diameter Aluminum Tube Pull Handles

UWAPNC UWAPFC (L Configurable)



RoHS10



Part Name	Material
Tube Handle	EN AW-6063 Equiv.
Elbow	Polycarbonate

L Fixed

Part Number Type	L	Applicable Screw	Unit Price
UWAPN (L Fixed)	150	Flat Head Screw M8	
	200		
	250		
	300		
	400		
	500		
600			

L Configurable

Part Number Type	L (mm increment)	Applicable Screw	Unit Price
UWAPF (L Configurable)	100-150	Flat Head Screw M8	
	151-200		
	201-250		
	251-300		
	301-400		
	401-500		
	501-600		

L Fixed

Part Number Type	L	Applicable Screw	Unit Price
UWAPNC (L Fixed)	100	Hex Socket Head Cap Screw M6	
	150		
	200		
	250		
	300		

L Configurable

Part Number Type	L (mm increment)	Applicable Screw	Unit Price
UWAPFC (L Configurable)	100-150	Hex Socket Head Cap Screw M6	
	151-200		
	201-250		
	251-300		

Ordering Example Part Number - L UWAPN 150 UWAPFC 185

* is not necessary for L Fixed Type.