

Fixed


■ **Features:** Hinge Bases in stock whose T (thickness) and H (height) to DH7 are selectable from two dimensions.

■ U-Shaped



RoHS10

Type	M Material	S Surface Treatment
HKNKJB	S45CEquiv.	Black Oxide




Part Number		T Selection	H Selection		W	A	F	E	K	S	d	C	Unit Price
Type	DH7												
HKNKJB	5	12	20	25	6	38	30	22	12	5	4.5	3	
		16										4	
	6	12	20	25								3	
		16										4	
	8	16	25	30	8	50	40	30	14	10	5.5	4	
		19										5	
	10	16	25	30	10	65	55	42				4	
		19										5	
	12	19	30	35	12				5				
		22							6				

■ **T-Shaped**




RoHS10

Type	M Material	S Surface Treatment
HKNKB	S45CEquiv.	Black Oxide



Part Number		T Selection	H Selection		W	A	F	S	d	C	Unit Price
Type	DH7										
HKNKB	5	12	20	25	6	25	18	5	4.5	3	
		16								4	
	6	12	20	25						3	
		16								4	
	8	16	25	30	8	32	25	10	5.5	4	
		19								5	
	10	16	25	30	10					4	
		19								5	
	12	19	30	35	12	5					
		22				6					



Hinge Plates


■ **Features:** Economical Square Type and Flexible Dimension R Type are available.

■ **Square**



RoHS10

HPAN



MMaterial: EN 1.0038 Equiv

Part Number	Unit Price
HPAN	

 Ordering Example


Part Number
HPAN

■ Type R



RoHS10


HPE



M Material: EN 1.0038 Equiv.

Part Number		L 10mm Increment	T Selection	R	H	Unit Price
Type	D					
HPE	8	40~100	9 12 15 16	11	22	
	10			12.5	25	
	12			16	32	
	16			19	38	
	20			25	50	




Alterations	Code	Spec.
 2-WCC The corners on both sides can be cut in any given length. WCC=1mm Increment $1 \leq WCC < H/2$	WCC	

■ Economy Type



RoHS10

Type	Material	Surface Treatment
JNPB	EN 1.0330 Equiv.	Trivalent Bright Chrom
JNPS	EN 1.4301 Equiv.	-



Part Number		B		T		ℓ1	ℓ2	N	Unit Price					
									JNPB		JNPS			
Type	A			JNPB	JNPS				T2.0	T4.5	T2.0	T4.0		
JNPB	30	10	20	2.0	2.0	5	4.5	5.5						
	40	10	20						30					
	50	10	20						30	40				
	60	10	20						30	40	50			
JNPS	70	10	20	30	40	50	10	5.5						
	80	10	20	30	40	50								
	90	10	20	30	40	50								
	100	10	20	30	40	50								
	110	10	20	30	40	50								
	120	10	20	30	40	50								

