

Plastic Pull Handles, Mounting Plates for Pull Handles

Outside Mount




Small Plastic Pull Handles - Outside Mount



RoHS10

UPCNN



Material

Glass Fiber Reinforced Nylon 6

Part Number	Allowable Load (N)	Mass (g)	Unit Price 1 ~ 19 pc(s).	Volume Discount Rate 20~50
-------------	--------------------	----------	--------------------------	----------------------------

UPCNN 200 25

For orders larger than indicated quantity, please check with WOS.



Ordering Example


Part Number

UPCNN

Plastic Pull Handles - Outside Mount



UPCN




Material

Glass Fiber Reinforced Nylon 6

Part Number		Handle Color	H	h	L	L1	R	C	Lr	Lc	Allowable Load (N)	Mass (g)	Unit Price							
Type	A												B (Black)				W (White), M (Orange), R (Red), G (Green)			
													1 ~ 9 pc (s).	10~14	15~19	20~50	1 ~ 9 pc (s).	10~14	15~19	20~50
UPCN	19	B (Black) W (White) M (Orange) R (Red) G (Green)	36	30	90	108.5	5.5	9.5	11	6	500	23								
			51	45									24							
	21		36	30	93.5	112	6.5	10.5	13	7			25							
			51	45									28							
	26		41	34	117	139			15				38							
			57	50			8.5	13.3		9			48							
	27		45	37	132	156			16				54							
			63	55									62							
	28		52	42	152	177	6.5	10.5	13	7			66			-		-		-
			50	42									68							
			71	63	179	204	8.5	13.3	17	9			86							

The default handle color is black unless specified. The default H dimension is A19-H36, A21-H36, A26-H41, A27-H45 or A28-H50 unless specified.



Ordering Example

Part Number

UPCN21


Handle Color

B

H

51


How to Mount on Aluminum Extrusions



How to Use Mounting Plates for Pull Handles

Use of mounting plates prevents cracks and distortion.

Effective for thin panels.




Mounting Plates for Pull Handles



RoHS10

UPCNAT



Material: EN 1.4301 Equiv.

Part Number		L	L1	A	B	N	Applicable Handle	Reference Mass (g)	Unit Price 1 ~ 9 pc (s).	Volume Discount Rate 10~200
Type										
UPCNAT	90	108.5	19	9.25		5.5	UPCN19	31		
	93.5	112	21			6.5	UPCN21	36		
	117	139	26	11			UPCN26	55		
	132	156	27	12		8.5	UPCN27	64		
	179	204	28	12.5			UPCN28	88		



Ordering Example

Part Number

UPCNAT117

Phenol Pull Handles / Cantilever Pull Handles / Plastic Pull Handles with Caps

Outside Mount




Phenol Pull Handles



RoHS10

UPCFAN



Material

Phenol Resin


Part Number		L	L1	h	H	R	C	Lc	Mass (g)	Unit Price
Type										
UPCFAN	90	111	29	50	6.5	10.5	6.5	88		
	114	135						108		
	120	141						116		
	140	161						131		
	160	181						145		
	180	201						164		
	200	221						178		

Cantilever Pull Handles




RoHS10

Type	Handles		Cap
	Material	Surface Treatment	Material
HHKP	Glass Fiber Reinforced Nylon (Mat Black)	-	Nylon 6 (Mat Black)
HHKA	EN AC-46100 Equiv.	Baked Paint (Silver)	Nylon 6 (Mat Gray)



Example



Screws and washers are not included.


Part Number		L	H	h	A	R	C	Lr	Lc	D	P	K	Allowable Load (N)		Mass (g)		Unit Price	
Type													HHKP	HHKA	HHKP	HHKA	HHKP	HHKA
HHKP (Plastic)	80	29	18	16	3	6	5	3	24	12	6	60	200	15	28			
HHKA (Aluminum)	100	35	19	20	4	8	6	4	28	12	8	90	320	29	56			
	147	50.5	30	29	6	11	9	6	38	19	9	150	500	78	170			

Plastic Pull Handles with Caps



UPCDG

(Nylon 6)



Material

Glass Fiber Reinforced Nylon 6

Part Number		L	L1	Allowable Load (N)	Mass (g)	Unit Price
Type						
UPCDG	90	133			30	
	94	138.5			33	
	117	160			36	
	132	175			39	



Ordering Example

Part Number

UPCFAN90

HHKP100


UPCDG132

Nuts for Pull Handles



RoHS10

HHPUW



Material: EN 1.4301 Equiv.

Part Number		Applicable Handle	Unit Price 1 ~ 9 pc (s).	Volume Discount Rate 10~100
Type	P			
HHPUW	90	UPCDG90		



Ordering Example

Part Number

HHPUW90