




6-Surface Milled / 6-Surface Milled Upper-Lower Surface Rotary Grinding



Part Number	Finish Method
SS6F	6-Surface Milled
SSAH	6-Surface Milled Upper-Lower Surface Rotary Grinding

Tolerance	A, B	~99mm	100~250	251~
		±0.2	±0.25	±0.4



M Material: EN 1.0038 Equiv.



Ordering Example

Part Number	-	A	-	B	-	T
SS6F	-	100	-	100	-	8
SSAH	-	100	-	100	-	8

■ Precision Standards

(Max. Value)

Item		SS6F	SSAH
Thickness Parallelism (per 100mm)		0.05	0.012
Flatness (per 100mm)	T5, 6	0.1	0.05
	T8~15	0.07	0.03
	T16~25	0.05	0.015
	T28~		0.012
Perpendicularity of Datum Plane		0.015 per 100mm	
Circumference Chamfering		C0.2~C0.5	C0.5~C1.0

■6-Surface Milled

[illegible]

6-Surface Milled Upper-Lower Surface Rotary Grinding

[illegible]