


# Thin Magnetic Catches / Ultrathin Magnetic Catches / Adjustable Magnetic Catches

# Low Dust Generation Magnetic Catches / Low Dust Generation Thin Magnetic Catches / Plastic Catches

**Thin Magnetic Catches** **MGCBU**



RoHS 10


10 pcs. per package. Order quantity should be noted.

Part Name	Material	Surface Treatment
Main Body	ABS Resin	-
Catch Plate	EN 1.0330 Equiv.	Chrome Plating
Magnet	Ferrite	-

Part Number	P	A	t	F	B	P1	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	L	1 ~ 9 pkg (s).									10-100
<b>MGCBU</b>											
49	34	17	6.5	16.5	24	13	0.9	15			
59	44	23.5	6.7	23	34	20	2.0	33			
70	55	24.5	7.7	24	45	30	3.5	49			

10 pcs. per package

**Ultrathin Magnetic Catches** **MGCM**




RoHS 10

There is no catch plate.


Part Name	Material	Surface Treatment
Main Body	EN 1.0330 Equiv.	Nickel Plating
Magnet	Neodymium	Nickel Plating

Part Number	No.	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).					10-100
<b>MGCM</b>						
1	1.5	12				
2	4	12				

Ordering Example Part Number **MGCM2**



**Adjustable Magnetic Catches** **AMGCB**




RoHS 10

Part Name	Material	Surface Treatment
Main Body	Polypropylene	-
Catch Plate	EN 1.0330 Equiv.	Chrome Plating
Magnet	Ferrite	-


Part Number	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate		
Type	1 ~ 9 pc (s).				10-19	20-100
<b>AMGCB</b>						
1	3.1	15				

**Features** - The magnet position can be adjusted in 5mm increments.

Ordering Example Part Number **AMGCB1**



**Low Dust Generation Magnetic Catches** **MGCC**



RoHS 10

No.	Part Name	Material
①	Main Body	Polyacetal
②	Catch Plate	EN 1.4016 Equiv.
③	Magnet	Neodymium Magnet

Part Number	No.	Retention Force (kgf)	Mass (g)	Color	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).						10-50
<b>MGCC</b>							
1	1.0	21	①Black				
2	1.4	22	②Gray				
3	2.0	24	③Milky White				
4	3.3	25	④White				


**Features**

- The magnet encapsulated structure is effective for preventing rust and dust intrusions.
- These magnetic catches are the best suited for use in clean rooms.

Catch Plate is not included for No. 4.

Ordering Example Part Number **MGCC3**

**Low Dust Generation Thin Magnetic Catches** **MGCCU**



RoHS 10

Catch plate is also plastic coated.

Part Name	Material
Main Body	Polyacetal
Catch Plate	EN 1.4016 Equiv.
Magnet	Neodymium Magnet


Part Number	No.	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).					10-100
<b>MGCCU</b>						
1	1	14				

**Features**

- Catch plate is also plastic coated to reduce particle generation further.

Ordering Example Part Number **MGCCU1**

**Plastic Catches** **JMCG**



RoHS 10

Part Name	Material
Female Side	Polyacetal
Male Side	Polyamide

Part Number	Retention Force (kgf)	Latching Force (kgf)	A	B	E	G	H	L	d1	d2	Mass (g)	Color	Unit Price
Type	1 ~ 50 pcs.												
<b>JMCG</b>													
1W	1.7	2.2	26	18	6	24.5	17	2.5	3.3x6	3.3	2	Milky White	
2B	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Black	
2W	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Milky White	

Ordering Example Part Number **JMCG1W**