


Configurable Plates - Copper / Brass
Price List
Chrome Copper / Brass Plates

High Accuracy Blocks
Guaranteed Perpendicularity of All Angles



(Ex.) For C28PL-255.3-100-10
A Dimension x Area Unit Price = Price

CCSPL (Chrome Copper 4-Surface Milled & Rolled)

Table with columns A, B, T, 5, 6, 8, 10, 12, 15, 20, 25, 30. Rows list dimensions for CCSPL plates.

C28PL (Brass Plates 4-Surface Milled & Rolled)

Table with columns A, B, T, 5, 6, 8, 10, 12, 15, 20, 25, 30. Rows list dimensions for C28PL plates.

CCSPF (Chrome Copper 6-Surface Milled)


Table with columns A, B, T, 3-3.9, 4-4.9, 5-5.9, 6-7.9, 8-8.9, 10-14.9, 15-19.9, 20-24.9, 25-30. Rows list dimensions for CCSPF plates.

C28PF (Brass Plates 6-Surface Milled)

Table with columns A, B, T, 3-3.9, 4-4.9, 5-5.9, 6-7.9, 8-8.9, 10-14.9, 15-19.9, 20-24.9, 25-30. Rows list dimensions for C28PF plates.



Table with columns Part Number, Thin, Standard, Material, Hardness. Rows list materials like U-SSFBG, U-SCFBG, U-PXSG, U-NAKSG.



Ordering Example
Part Number - A - B - T
U-SCFBG - 99.9 - 10.1 - 3.01
SSFBG - 30.5 - 20.6 - 17.13

Thin (T=3 ~ 9.99mm)

Table with columns A, B, T: 0.01mm Increment. Rows list dimensions for thin plates.

Standard (T=10 ~ 60mm)

Table with columns A, B, T: 0.01mm Increment. Rows list dimensions for standard plates.