

Adjustable Draw Latches / Corner Draw Latches / Bar Latches / Cam Locks

Rotating Latches / Latches for Airtight Seals / Barrel Slide Bolt Latches / Slide Bar Latches

Adjustable Draw Latches

PKWSAJ1 3-Through Ø5.3, Countersink Ø 10.3
 2-Through Ø5.3, Countersink Ø 10.3
 Adjustable Range (97-120)
 Adjustable Range (57-80)
 Mounting Pitch Adjustable Range (57-80) 17

PKWSAJ2 2-Through Ø5.3, Countersink Ø 10.3
 Adjustable Range (97-120)
 2-Through Ø5.3, Countersink Ø 10.3
 Adjustable Range (62-85)
 Mounting Pitch Adjustable Range (62-85) 15

Material Surface Treatment
 EN 1.4301 Equiv. Buffing

Part Number	No.	* Pull Force N (kgf)	Mass (g)	Unit Price	Volume Discount Rate
Type				1 ~ 9 pc (s).	10 ~ 29 30 ~ 49 50 ~ 200
PKWSAJ	1	588 (60)	100		
	2	588 (60)	90		

* Pull force is for 1mm pull distance.

Corner Draw Latches

PKBSK1 In-line Catch Type (Stainless Steel)
 Right Angle Catch Type **PKBSK2** (Stainless Steel)

The dimensions are for 0mm pull distance.

Material Surface Treatment
 EN 1.4301 Equiv. Electrolytic Polishing

Part Number	No.	* Pull Force N (kgf)	Mass (g)	Unit Price	Volume Discount Rate
Type				1 ~ 9 pc (s).	10 ~ 19 20 ~ 100
PKBSK	1	44 (4.5)	56		
	2				

* Pull force is for 1mm pull distance.

Bar Latches

HHMU

Material Surface Treatment
 EN 1.4301 Equiv. Electrolytic Polishing

Cam Locks

LOCNL

Key removable 1 location
 Key removable 2 locations

Part Name **Material** **Surface Treatment**
 Main Body Zinc Die Cast Chrome Plating
 Hex Nut EN 1.0330 Equiv. Trivalent Chromate
 Lock Plate EN 1.0330 Equiv. Trivalent Chromate
 Key (2 pcs. included) EN 1.0330 Equiv. Chrome Plating

• Mass: 25g

Material Surface Treatment
 EN 1.4301 Equiv. Buffing

Ordering Example Part Number
 PKWSAJ1
 PKBSK2
 LOCNL1

Rotating Latches

LCR LCL

The photo is for right-hand use.

Material Surface Treatment
 EN 1.4301 Equiv. Buffing

Part Number	Mass (g)	Unit Price
Type	L	
LCR (For Right-hand Use)	80	100
LCL (For Left-hand Use)	100	130

Ordering Example Part Number **LCR80**

Latches for Airtight Seals

LCAR LCAL

The photo is for left-hand use.

Material Surface Treatment
 EN 1.4301 Equiv. Buffing

Part Number	No.	(L)	(L-1)	L2	L3	L4	W	W1	(H)	H1	(H2)	H3	P	P1	P2	(P3)	Mass (g)	Unit Price
LCAR (For Right-hand Use)	11	89	65.5	30	30	20	55	45	30	12.5	14.5	10	37	17	32	28	150	
	16	113	85.5	30	30	20	60	45	40	13	14.5	10	40	20	32	28	194	
LAL (For Left-hand Use)	20	125	98	32	31.5	23	65	50	40	14	17	11	43	22	35	30	210	
	25	140	109	40	35	24	80	50	46.5	14.5	18	13	52	25	34	34	290	
	30	170	127	45	40	28	90	52	50.8	16.8	19	14.5	70	34	40	43	450	

Ordering Example Part Number **LCAR16**

Barrel Slide Bolt Latches

HHMT

Material EN 1.4301 Equiv.

Part Number	Type	L	W	P	P1	D	d	T	t	t1	A
HHMT	90	40	60	28	7.5	9	12	2.4	5.7	20	
	125	40	95	28	7.5	9	12	2.4	5.7	20	
	180	60	140	40	10	13	16	3	8	25	

Part Number	Type	S	F	J	N	Mass (g)	Unit Price	Volume Discount Rate
		L				(g)	1 - 9 pc (s).	10 - 50
HHMT	90	20	20	15	5	128		
	125	20	20	15	5.2	167		
	180	30	25	20	6.2	451		

Slide Bar Latches

HHMSQ

Material EN 1.4301 Equiv.

Part Number	Type	L	P	P1	P2	W	W1	d	(S)	A	T	t	H	h
HHMSQ	50	34	25	28	38	38	13	12.5	12	12.5	4	27	12	
	65	47	31	32	45	45	15	15	15	13.5	5	28	12.5	

Part Number	Type	N	Mass (g)	Unit Price	Volume Discount Rate
		Through Countersink	(g)	1 - 9 pc (s).	10 - 49 50 - 200
HHMSQ	50	3.5	7	58	
	65	5	9	100	

Ordering Example Part Number **HHMT90**
HHMSQ65