





Parallel Keys
-Blank Type-

Price Reduction
10% on average



Tapered Machine Keys with Gib Head

CAD Data




Part Number		Tolerance (h9)	h	H Tolerance	C	€ Unit Price Qty. 1-3	Volume Discount		
Type	B						4-19	20-49	50-100
KET	3	0 -0.025	3	0 -0.025	0.16~0.25				
	4		4						
	5	0 -0.030	5	0 -0.030					
	6		6						
	7		7	0 -0.036	0.25~0.40				
	8	0 -0.036							
	10		8						
	12		9	0 -0.090					
	14		10		0.40~0.60				
	15	0 -0.043							
	16		11	0 -0.110					

Order Example

Part Number
KET10

Days to Ship
6 Days P87





Part Number		h	C	€ Unit Price Qty. 1-3	Volume Discount		
Type	B				4-19	20-49	50-100
KETS	2		0.2				
	3						
	4						
	5						
	6	+0.015 -0.025	0.3				
	7						
	8						
	10						
	12		0.5				
	14						

Order Example

Part Number - h
KETS8 - 7

Days to Ship
6 Days P87



Part Number		h	L	h1	h2 / f	(e)	C	€ Unit Price Qty. 1-4	Volume Discount		
Type	Bh9								5-9	10-29	30-49
4		4	30	7	4	4	0.16~0.25				
5	0 -0.030	5	40	8	5	5					
6		6	45	10	6	6	0.25~0.40				
7		7.2	50		7	7					
8	0 -0.036	8	60	11	8	8					
10		8	75	12	8	10					
12		8	90		8	12	0.40~0.60				
14		9	110	14	9	14					
15	0 -0.043	10.2	110	15	10	15					
16		10	120	16	10	16					
18		11	135	18	11	18					
20		12	150	20	12	20	0.60~0.80				
22		14	170	22	14	22					
24	0 -0.052	16.2	180	24	16	24					
25		14	200	22	14	25					
28		16	210	25	16	28					
32		18	240	28	18	32					
35	0 -0.062	22.3	260	32	22	35	1.00~1.20				
36		20	280		20	36					
38		24.3	285	36	24	38					

Order Example



Part Number
KTH12

Days to Ship
8 Days

Express A 2,00 EUR / piece P88

A Express Charge of 5,40 EUR for 3 or more identical pieces.

	Alterations		Part Number - (LC)
		KTH10	LC60

Alteration	Code	Spec.	Price Adder																				
L Dimension Change  	LC	LC=1 mm Increment LC(Min.)≤LC≤L For LC(Min.), see below. <table><tr><th>B</th><th>LC (Min.)</th></tr><tr><td>4 - 5</td><td>10</td></tr><tr><td>6 - 7 - 8</td><td>15</td></tr><tr><td>10 - 12</td><td>20</td></tr><tr><td>14 - 15 - 16</td><td>22</td></tr><tr><td>18 - 20</td><td>25</td></tr><tr><td>22 - 24 - 25</td><td>30</td></tr><tr><td>28</td><td>35</td></tr><tr><td>32 - 35 - 36</td><td>40</td></tr><tr><td>38</td><td>45</td></tr></table>	B	LC (Min.)	4 - 5	10	6 - 7 - 8	15	10 - 12	20	14 - 15 - 16	22	18 - 20	25	22 - 24 - 25	30	28	35	32 - 35 - 36	40	38	45	2,00
B	LC (Min.)																						
4 - 5	10																						
6 - 7 - 8	15																						
10 - 12	20																						
14 - 15 - 16	22																						
18 - 20	25																						
22 - 24 - 25	30																						
28	35																						
32 - 35 - 36	40																						
38	45																						