

Table-Top Bases

CAD Data

Table-Top Bases RoHS10 **NFB**

Material: PP Resin (Pad)
1.0038/S235JR (Threads)
Surface Treatment: Trivalent Chromate

Ⓜ Material: PP Resin (Pad)
1.0038/S235JR (Threads)
Ⓢ Surface Treatment: Trivalent Chromate

Ⓢ Screws and pads are one-piece.

Part Number Type	M Coarse	A				ℓ	E	Allowable Load (kN)	€ Unit Price
NFB	20	5	14	18	23	28	4	0.7	
		6	17	22	27	32	5	1.0	
	30	6	17	22	27	32	5	1.2	
		8	21	26	31	36	6.5	1.8	
	40	8	21	26	31	36	6.5	2.0	
		10	25	30	35	40	8	2.1	

Order Example: Part Number - M - A
NFB30 - 6 - 27

Days to Ship: 6 Days

Price

Volume Discount (Round down to one Cent.) P87

Qty.	1-19	20-34	35-49	50-99
Rate	€ Unit Price	5%	10%	18%

For orders larger than indicated quantity, please request a quotation.

Table-Top Bases RoHS10 **KFB** (Separate Type) **KFBR** (Knurled Type)

Material: ABS Resin (KFB), Polyamide (KFBR), Polyurethane (KFBR)
Bolt: JIS SWRM
Surface Treatment: Trivalent Chromate

Ⓜ Material: ABS Resin (KFB), Polyamide (KFBR), Polyurethane (KFBR)
Bolt: JIS SWRM
Ⓢ Surface Treatment: Trivalent Chromate

Ⓢ Separable threads and pad are convenient for disposal.

Part Number Type	M (Coarse)	A	ℓ	E	Allowable Load (kN)	Mass (g)	€ Unit Price
KFB	40	8	25	2	0.28	24	
	50	10		3		28	
	60	12		15		30	
KFBR	40A	8	24	23	0.78	35	
	40B	8	32	54		71	
	50A	10	25.5	24		58	
	50B	10	32	54		114	
	60	10	26	24		68	

Order Example: Part Number - M - A
KFB50 - 10 - 25

Days to Ship: 6 Days

Price

Volume Discount (Round down to one Cent.) P87

Qty.	1-49	50-99	100-199
Rate	€ Unit Price	5%	10%

For orders larger than indicated quantity, please request a quotation.

Lifting Units

CAD Data

Standard Type **JFCK** **JFCKB** (Black)

Hole Type **JFCN** **JFCNB** (Black)

Tip Enlarged View

Ⓢ A handle with a square hole can be used on the end MBCH (P.1013).
Ⓢ JFCN and JFCNB have mounting holes 4-d on both top and bottom surfaces.

Type	Material	Surface Treatment
Standard Type		
JFCK		Trivalent Chromate
JFCKB	1.1191/C45E	Trivalent Chromate (Black)

Part Number Type	No.	Pre-drilled Hole Type		Stroke (H)	A	K	E	L	t	Static Allowable Load (kN)	Mass (g)	€ Unit Price			
		JFCN · JFCNB										Standard Type		Hole Type	
		1mm Increment										JFCK	JFCKB	JFCN	JFCNB
Standard Type	15	30~100	30~60	95	247	150	26.6	177	1.6	0.49	2220				
	20	30~150	30~100	106	334	200		19				227			
Hole Type	25	30~200	30~150	128	432	250	32.3	276	2.3		4960				

Order Example: Part Number - F - G
JFCK20 - 188 - 140

Days to Ship: 8 Days

ex Example

It is usable to adjust heights of work platform etc.

Ⓢ Ensure that no loads are applied while lifting or lowering.

Square / Round Hole Handle P.1013