


BAFFLE BOARDS

—PARALLEL THREAD PLUG TYPE / O-RING SEAL TYPE—

Parallel thread plug type



D—BFPF (Metric thread)
D—BFPFG (Parallel pipe thread)



M C3604

Metric thread type

ℓ	B	M×P	T	Part No.		L	
				Type	A		
8	4	M8×0.75	1.5	D—BFPF	6	100	200
	5	M10×1.0			8		
	6	M12×1.5	10		125	250	
10	7	M14×1.5	2.0		12	150	300
	8	M16×1.5		14			

⚠ Make the water hole diameter to which D—BFPF is fitted at least 0.5~1mm-larger than A. ⚠ Discoloration may occur at the welding position.

Parallel pipe thread type

ℓ	B	G(PF)	T	Part No.		L	
				Type	A		
8	5	G1/8	1.5	D—BFPFG	8.5	100	200
10	7	G1/4	2.0		11.5	125	250
	8	G3/8			15	150	300

⚠ Make the water hole diameter to which D—BFPFG is fitted at least 0.5~1mm-larger than A.



Order

Part No.

D—BFPF8

D—BFPFG11.5

L

200

250



Days to Ship



Stock



Price

Order / Quote:


WOS: <https://in.misumi-ec.com/>

TEL:+91-124-468-8800 E-mail:cs@misumi.co.in

O-Ring seal type



D—BFBM



M C3604

O-ring: Fluoric rubber

D	(L-ℓ)	L	ℓ	ℓ1	M	T	Part No.	
							Type	A
11.9	180	193	13	10	M6	1.5	D—BFBM	8
								10
								12
15.8	250	266	16	11.5	M8	2.0		15

⚠ Make the water hole diameter to which D—BFBM is fitted at least 0.5~1mm-larger than A. ⚠ Discoloration may occur at the welding position.



Order

Part No.

D—BFBM10



Days to Ship



Stock



Price

Order / Quote:

WOS: <https://in.misumi-ec.com/>

TEL:+91-124-468-8800 E-mail:cs@misumi.co.in

