

DIN 1530
1.2344 equivalent
+
Nitrided



STRAIGHT EJECTOR PINS

—STANDARD TYPE—

DIN 1530
1.2344 equivalent
+
Nitrided

STRAIGHT EJECTOR PINS

—L/L · P DIMENSION SPECIFY TYPE—



Standard

H	T	P g6	Part No.		L Selection										
			Type	P											
2.5	1.2	-0.002 -0.008	D-EPN	1	100	125	160	200							
				1.1	100	125	160	200							
				1.2	100	125	160	200							
3	1.5	-0.002 -0.008	D-EPN	1.5	100	125	160	200	250						
				1.8	100	125	160	200							
4	2	-0.004 -0.012	D-EPN	2	100	125	160	200	250	315					
5				100	125	160	200	250	315	400					
6	3	-0.004 -0.012	D-EPN	3	100	125	160	200	250	315	400	500			
7				100	125	160	200	250	315	400					
8				100	125	160	200	250	315	400	500	630			
10	5	-0.005 -0.014	D-EPN	4.5	100	125	160	200	250	315	400	500	630	800	1000
5				100	125	160	200	250	315	400	500				
5.5				100	125	160	200	250	315	400	500				
12	7	-0.006 -0.017	D-EPN	6	100	125	160	200	250	315	400	500	630	800	1000
				6.5	100	125	160	200	250	315	400	500			
				7	100	125	160	200	250	315	400	500			
14	7	-0.006 -0.017	D-EPN	7.5	100	125	160	200	250	315	400	500			
				8	100	125	160	200	250	315	400	500	630	800	1000
				8.5	100	125	160	200	250	315	400	500			
16	7	-0.006 -0.017	D-EPN	9	100	125	160	200	250	315	400	500	630		
				9.5	100	125	160	200	250	315	400	500			
				10	100	125	160	200	250	315	400	500	630	800	1000
18	7	-0.006 -0.017	D-EPN	10.5	100	125	160	200	250	315	400	500			
				11	100	125	160	200	250	315	400	500			
				12	100	125	160	200	250	315	400	500	630	800	1000
22	8	-0.007 -0.020	D-EPN	12.2	125	160	200	250	315	400	500	630			
				12.5	100	125	160	200	250	315	400	500			
				14	100	125	160	200	250	315	400	500	630		
24	8	-0.007 -0.020	D-EPN	16	100	125	160	200	250	315	400	500	630	800	1000
				18	125	160	200	250	315	400	500	630	800	1000	
				20	100	125	160	200	250	315	400	500	630	800	1000
26	8	-0.007 -0.020	D-EPN	20	100	125	160	200	250	315	400	500	630	800	1000
				25	125	160	200	250	315	400	500	630			

Order Part No. — L
D-EPN 3 — 100

L Dimension Specify

H	T	P g6	Part No.		L	
			Type	P	0.01mm increments	
2.5	1.2	-0.002	D-EPN-L	1	40.00 ~ 200.00	
				1.5	40.00 ~ 200.00	
3	1.5	-0.008	D-EPN-L	2	40.00 ~ 315.00	
				2.5	40.00 ~ 315.00	
4	2	-0.004	D-EPN-L	3	40.00 ~ 400.00	
				3.5	40.00 ~ 400.00	
5	2	-0.012	D-EPN-L	4	40.00 ~ 500.00	
				4.5	40.00 ~ 250.00	
6	3	-0.004	D-EPN-L	5	40.00 ~ 400.00	
				5.5	40.00 ~ 200.00	
7	3	-0.012	D-EPN-L	6	40.00 ~ 1000.00	
				6.5	100.00 ~ 250.00	
8	3	-0.004	D-EPN-L	8	100.00 ~ 1000.00	
				10	100.00 ~ 500.00	
10	5	-0.005	D-EPN-L	12	100.00 ~ 1000.00	
				14	100.00 ~ 500.00	
12	5	-0.014	D-EPN-L	16	100.00 ~ 1000.00	
				18	100.00 ~ 1000.00	
14	7	-0.006	D-EPN-L	20	100.00 ~ 1000.00	
				22	100.00 ~ 500.00	
16	7	-0.017	D-EPN-L	25	100.00 ~ 500.00	
				26	100.00 ~ 500.00	
18	8	-0.007	D-EPN-L			
				32	100.00 ~ 500.00	

Alterations Part No. — L — P — (KC · WKC...etc.)
D-EPNB 4.5 — 248.35 — P4.23 — WKC2.115

Alterations	Code	Spec.
	KC	Single flat cutting P/2 ≤ KC < H/2 (1) To align the key flat with the shaft diameter [Unit of designation] 0.005mm increments possible
	WKC	Two flats cutting P/2 ≤ WKC < H/2 (2) To designate arbitrary key flat dimensions [Unit of designation] 0.1mm

L · P Dimension Specify

H	T	P g6	Part No.		L		P	
			Type	No.	0.01mm increments	0.01mm increments		
2.5	1.2	-0.002	D-EPNB	1	40.00 ~ 200.00	0.50 ~ 1.00		
				1.5	40.00 ~ 200.00	1.01 ~ 1.50		
3	1.5	-0.008	D-EPNB	2	40.00 ~ 315.00	1.51 ~ 2.00		
				2.5	40.00 ~ 315.00	2.01 ~ 2.50		
4	2	-0.004	D-EPNB	3	40.00 ~ 400.00	2.51 ~ 3.00		
				3.5	40.00 ~ 400.00	3.01 ~ 3.50		
5	2	-0.012	D-EPNB	4	40.00 ~ 500.00	3.51 ~ 4.00		
				4.5	40.00 ~ 250.00	4.01 ~ 4.50		
6	3	-0.004	D-EPNB	5	40.00 ~ 400.00	4.51 ~ 5.00		
				5.5	40.00 ~ 200.00	5.01 ~ 5.50		
7	3	-0.012	D-EPNB	6	40.00 ~ 1000.00	5.51 ~ 6.00		
				6.5	100.00 ~ 250.00	6.01 ~ 6.50		
8	5	-0.005	D-EPNB	8	100.00 ~ 1000.00	6.51 ~ 8.00		
				10	100.00 ~ 500.00	8.01 ~ 10.00		
10	5	-0.014	D-EPNB	12	100.00 ~ 1000.00	10.01 ~ 12.00		
				14	100.00 ~ 500.00	12.01 ~ 16.00		
12	7	-0.006	D-EPNB	16	100.00 ~ 1000.00	16.01 ~ 20.00		
				20	100.00 ~ 500.00	20.01 ~ 25.00		
14	7	-0.017	D-EPNB	25	100.00 ~ 500.00	20.01 ~ 25.00		
				26	100.00 ~ 500.00			

Alteration details P.4
Alterations Code Spec.
 HC HC=0.1mm increments
P+1 ≤ HC < H, P ≥ 1.5
Order Part No. — L — P
D-EPN-L 1 — 100.00
D-EPNB 1 — 100.00 — P0.50